



Engineer Drawing



SPECIFICATIONS:

Voltage Rating:250V AC/DC

Current Rating:2.5A AC/DC

Withstanding Voltage:1000V AC/minute




Temperature Range:-25℃ To +85℃

Insulation Resistance:1000mΩ Min

Contact Resistance:20mΩ Max



Material:PA66 UL94V-0

Color:Black



IPCW 254 H X X X X XX X

Poles	Dimensions	
	A	B
02P	5.08	2.54
03P	7.62	5.08
04P	10.16	7.62
05P	12.70	10.16
06P	15.24	12.70
07P	17.78	15.24
08P	20.32	17.78
09P	22.86	20.32
10P	25.40	22.86
11P	27.94	25.40
12P	30.48	27.94
13P	33.02	30.48
14P	35.56	33.02
15P	38.10	35.56
16P	40.64	38.10
17P	43.10	40.64
18P	45.64	43.18
20P	50.72	48.26



Series Type

Pitch:2.54mm

Connector Type

Rows Code

Other Code

Pin Code

Material Code

Colour Code

Internal Code

GENERAL
TOLERANCES:
X.=±0.30
X.X=±0.20
X.XX=±0.10

NCP

www.i-ncp.com

PART NO:
IPCW254H1 xx 7E0

NAME:

DRAWING NO
IPCW254H17E0

2.54mm Crimp Style Connectors

SHEET 1 OF 1

UNITS:mm SCALE:1:1 REV.01