




RoHS

REV	ECN NO.	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	新版发行			2025.03.19

- SPECIFICATIONS
- Current rating: 1A AC, DC
 - Temperature range: -40°C ~ +105°C
 - Insulation resistance: 1000MΩ Min.
 - Withstanding voltage: 500V AC/ minute.
 - Contact resistance: 20mΩ Max.

Material:
Insulator Material:LCP (UL 94V-0)
Contact Material:Brass
Plating: Au of Sn Over Ni

Ordering Code:
BH127VS-12-20-H25-L70
1 2
1.序列号
2.Pin位数: 2x10=20P

X.±0.50	X.°±	PART NO: BH127VS-12-20-H25-L70		XFCN 兴飞连接器	
.X±0.25	.X°±				
.XX±0.15	.XX°±	TITLE: 筒牛 1.27mm SMD 2x10P H2.5带围墙 SMD5.8mm 镀金 LCP 管装		0769-82001899	
.XXX±0.10	.XXX°±			www.xfconn.com	
UNITS:	mm			DWG NO: /	
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED,COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN		APPD	Chen ZhiQiang	VIEW 	
		CHKD	Liu Wei		
		DRAW	Chen HongJiang	SCALE	SHEET
		DATE	2025.03.19	NONE	1/1
					REV A1