





RoHS



PCB LAYOUT

SPECIFICATIONS

1. Current rating: 1A AC, DC
2. Temperature range: -40°C ~ +105°C
3. Insulation resistance: 1000MΩ Min.
4. Withstanding voltage: 500V AC/ minute.
5. Contact resistance: 20mΩ Max.

Material:

Insulator Material:LCP (UL 94V-0)

Contact Material:Brass


Plating: Au of Sn Over Ni

Ordering Code:

BH127VS-12-10-H25-L70-R
1 2

1.序列号

2.Pin位数: 2x05=10P



卷装图

X.±0.50	X.°±	PART NO: BH127VS-12-10-H25-L70-R		XFCN 兴飞连接器		
.X±0.25	.X°±					
.XX±0.15	.XX°±	TITLE: 筒牛 1.27mm SMD 2x05P H2.5带围 墙 SMD5.8mm 镀金 LCP 加盖卷装		0769-82001899		
.XXX±0.10	.XXX°±			www.xfconn.com		
UNITS:	mm			DWG NO: /		
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED,COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN		APPD	Chen ZhiQiang			
		CHKD	Liu Wei	VIEW		
		DRAW	Chen HongJiang	SCALE	SHEET	REV
		DATE	2025.03.05	NONE	1/1	A1