

Description:



This N-Channel MOSFET uses advanced SGT technology and

design to provide excellent $R_{DS(on)}$ with low gate charge.

It can be used in a wide variety of applications.

Features:

- 1) $V_{DS}=100V, I_D=5A, R_{DS(on)} < 120m\Omega @ V_{GS}=10V$ (Type: $90m\Omega$)
- 2) Low gate charge.
- 3) Green device available.
- 4) Advanced high cell density trench technology for ultra low $R_{DS(on)}$.
- 5) Excellent package for good heat dissipation.
- 6) MSL3



Package Marking and Ordering Information:

Part NO.	Marking	Package	Packing
DO5T10BA	5T10B.	SOT-23-3	3000pcs/Reel

Absolute Maximum Ratings: ($T_A=25^\circ\text{C}$ unless otherwise noted)

Symbol	Parameter	Ratings	Units
V_{DS}	Drain-Source Voltage	100	V
V_{GS}	Gate-Source Voltage	± 20	V
I_D	Continuous Drain Current- $T_A=25^\circ\text{C}$	5	A
	Continuous Drain Current- $T_A=100^\circ\text{C}$	3	
I_{DM}	Pulsed Drain Current ¹	12	
P_D	Power Dissipation	1.3	W
T_J, T_{STG}	Operating and Storage Junction Temperature Range	-55-+150	$^\circ\text{C}$

Thermal Characteristics:

Symbol	Parameter	Max	Units
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient	96	$^\circ\text{C}/\text{W}$


Electrical Characteristics: ($T_A=25^{\circ}\text{C}$ unless otherwise noted)

Symbol	Parameter	Conditions	Min	Typ	Max	Units
Off Characteristics						
BV _{DSS}	Drain-Sourtce Breakdown Voltage	V _{GS} =0V, I _D =250 μ A	100	---	---	V
I _{DSS}	Zero Gate Voltage Drain Current	V _{GS} =0V, V _{DS} =100V	---	---	1	μ A
I _{GSS}	Gate-Source Leakage Current	V _{GS} =± 20V, V _{DS} =0A	---	---	± 100	nA
On Characteristics						
V _{GS(th)}	Gate-Source Threshold Voltage	V _{GS} =V _{DS} , I _D =250 μ A	1.2	1.6	2.5	V
R _{DS(ON)}	Drain-Source On Resistance ³	V _{GS} =10V, I _D =3A	---	90	120	m Ω
		V _{GS} =4.5V, I _D =2A	---	120	150	m Ω
Dynamic Characteristics						
C _{iss}	Input Capacitance	V _{DS} =50V, V _{GS} =0V, f=1MHz	---	150	---	pF
C _{oss}	Output Capacitance		---	65	---	
C _{rss}	Reverse Transfer Capacitance		---	7	---	
Switching Characteristics						
t _{d(on)}	Turn-On Delay Time	V _{DS} =50V, I _D =3A, R _{ENG} =2 Ω ,V _{GS} =10V	---	16	---	ns
t _r	Rise Time		---	4.1	---	ns
t _{d(off)}	Turn-Off Delay Time		---	25	---	ns
t _f	Fall Time		---	2.9	---	ns
Q _g	Total Gate Charge	V _{GS} =10V, V _{DS} =50V, I _D =3A	---	4.8	---	nc
Q _{gs}	Gate-Source Charge		---	1.63	---	nc
Q _{gd}	Gate-Drain “Miller” Charge		---	1.3	---	nc
Drain-Source Diode Characteristics						
V _{SD}	Diode Forward Voltage	V _{GS} =0V, I _{SD} =3A	---	---	1.3	V
I _S	Continuous Drain Curren	V _D =V _G =0V	---	---	5	A
I _{SM}	Pulsed Drain Current		---	---	12	A

Notes:


1. Repetitive Rating: Pulse Width Limited by Maximum Junction Temperature
2. EAS condition : $T_J=25^{\circ}\text{C}, V_{DD}=50V, V_G=10V, L=0.5mH$
3. Pulse Test: Pulse Width $\leq 300\mu s$, Duty Cycle $\leq 0.5\%$

SOT-23-3 Package Outline Data




Tape & Reel Information

Dimensions in mm




PKG TYPE	W	P	E	F	D	D1	Po	Po10	P2	A0	B0	K0	T
SOT23-3	8.00	4.00	1.75	3.50	1.50	1.00	4.00	40.00	2.00	3.13	3.22	1.30	0.20
Tolerance	± 0.2	± 0.1	± 0.1	± 0.1	± 0.1	± 0.1	± 0.1	± 0.2	± 0.1	± 0.1	± 0.1	± 0.1	± 0.03



Pulling direction 

Marking Information:



Previous Version

Version	Date	Subjects (major changes since last revision)
1.0	2024-10-08	Release of final version

Attention :

- Information furnished in this document is believed to be accurate and reliable. However, Shenzhen Doingter Semiconductor Co.,Ltd. assumes no responsibility for the consequences of use without consideration for such information nor use beyond it.
- Information mentioned in this document is subject to change without notice, apart from that when an agreement is signed, Shenzhen Doingter complies with the agreement. Products and information provided in this document have no infringement of patents.
- Shenzhen Doingter assumes no responsibility for any infringement of other rights of third parties which may result from the use of such products and information. This document supersedes and replaces all information previously supplied.  Is a registered trademark of Shenzhen Doingter Semiconductor Co., Ltd. Copyright © 2013 Shenzhen Doingter Semiconductor Co.,Ltd. Printed All rights reserved.