







NOTES

MATERIAL

1. HOUSING MATERIAL: PBT BLACK UL94V-0.
2. CONTACT MATERIAL: PHOSPHOR BRONZE $\phi 0.46\text{mm}$.
3. PLATING: GOLD FLASH PLATING OVER NICKEL.
4. SHIELD: 0.20mm THICKNESS COPPER ALLOY WITH NICKEL PLATED.

ELECTRICAL

1. VOLTAGE RATING: 125 VAC RMS.
2. CURRENT RATING: 1.5 AMP.
3. CONTACT RESISTANCE: 40 MILLIOHMS MAX.
4. INSULATION RESISTANCE: 500 MEGOHMS MIN @ 100V DC.
5. DIELECTRIC DIELECTRIC RESISTANCE: 500V DC RMS 50Hz. 1MIN.

MECHANICAL

1. DURRABILITY: 750 CYCLES MIN.
2. MATING/UNMATING FORC: 2.24 KG.F MAX.

ENVIRONMENTAL:

1. OPERATION: $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$.
2. STORAGE: $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$.

PCBLAYOUT
TOL: ± 0.05

UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS: ANGLES:
X : ± 0.30 X : $\pm 2^{\circ}$
X.X : ± 0.20 X.X : $\pm 1^{\circ}$
X.XX : ± 0.10



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE	5921 1x2无弹F3.05 DIP有后脚			
DWN	xiong	PART NO. RJ3506-003-11		
CHKD	lee	SCALE: 1:1	UNIT: mm	
APVD	wang	SIZE: A4	SHEET: 10F 1	REV: A4

CUSTOMER COPY