







MATERIAL:

HOUSING: PA46, PBT, BLACK.
TERMINAL: PHOSPHOR BRONZE Ø0.46MM
G/FU*GOLD PLATING

SHIELD: C2680, T=0.20MM, 20 MIN NICKEL PLATING
NO ALL AREA

MACHANICAL:



DURABILITY: 750 CYCLES MIN, 12.5MM/MINUTE.
INSERTION FORCE: 2.2KG.F MAX.
RETENTION STRENGTH: 7.7KG.F BETWEEN JACK AND PLUG
OPERATING TEMPERATURE: -40 °C ~ +85 °C.
STORAGE TEMPERATURE: -40 °C ~ +85 °C.
ALL CRITICAL DIMENSIONS WITH **

ELECTRICAL:

VOLTAGE: 125 VOLTS AC.
CURRENT RATING: 1.5AMP.
DIELECTRIC STRENGTH: 1000 VAC RMS 50HZ OR 60HZ, 1 MIN.
INSULATION RESISTANCE: 500 MEGA OHMS MIN. INITIAL
AFTER 500V DC FOR 1 MINUTE.
CONTACT RESISTANCE: SINGLE TERMINAL 30 MILLIOHMS MAX.
INITIAL 50 MILLIOHMS MAX. AFTER
DURABILITY TEST.

LED Specification

Standard LED Color	LED Wavelength	Forward(A)	Forward(V)
Green	568nm	20mA	1.6-2.6V
Yellow	585nm	20mA	1.6-2.6V



			GENERAL TOLERANCE	制 图 DRAWING	04	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM TOL	审 核 CHECK					
			X.X ±0.30	批 准 APPROVAL					
			X.XX ±0.20	比 例 SCALE					
1	初版发行		X.XXX ±0.10	投 影 Projection		产品名称 TITLE	网络插座	版 本 REV.	A
序号 No.	变更内容 MODIFY CONTENT	日 期 MODIFY DATE	Angle ±3.0°			产品料号 PART NO.	HC-RJ45-5JA-5-2	单 位 UNITS	mm
						材 料 MATERIAL		页 次 SHEET	1/1