







- PCB SIDE TO PHY
- 1 ○ ○ J1
- 2 ○ ○ J2
- 3 ○ ○ J3
- 4 ○ ○ J4
- 5 ○ ○ J5
- 6 ○ ○ J6
- 7 ○ ○ J7
- 8 ○ ○ J8
- CABLE SIDE

MATERIAL:
HOUSING:PA46,PBT,BLACK.
TERMINAL: PHOSPHOR BRONZE Ø0.46MM
6/FU*GOLD PLATING

SHIELD:C2680,T=0.20MM, 20 MIN NICKEL PLATING
NO ALL AREA

MACHANICAL:
DURABILITY: 750 CYCLES MIN,12.5MM/MINUTE.
INSERTION FORCE: 2.2KG.F MAX.
RETENTION STRENGTH : 7.7KG.F BETWEEN JACK AND PLUG
OPERATING TEMPERATURE: -40℃~+85℃.
STORAGE TEMPERATURE: -40℃~+85℃.
ALL CRITICAL DIMENSIONS WITH "H"

ELECTRICAL:
VOLTAGE: 125 VOLTS AC.
CURRENT RATING : 1.5AMP.
DIELECTRIC STRENGTH : 1000 VAC RMS 50HZ OR 60HZ,1 MIN.
INSULATION RESISTANCE: 500 MEGA OHMS MIN. INITIAL
AFTER 500V DC FOR 1 MINUTE.
CONTACT RESISTANCE: SINGLE TERMINAL 30 MILLIOHMS MAX.
INITIAL 50 MILLIOHMS MAX. AFTER
DURABILITY TEST.

			GENERL TOLERANCE		制 图	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	审 核				
			X.X	±0.30	批 准				
1	初版发行		X.XX	±0.20	比 例	产品名称	网络插座	版 本	A
序号	变更内容	日 期	X.XXX	±0.10	SCALE	产品料号	HC-RJ45-5JA-3-4	单 位	mm
No.	MODIFY CONTENT	MODIFY DATE	Angle	±3.0°	投 影	PART NO.		页 次	1/1
					Projection	材料		SHEET	