










RoHS  
Compliant  
2011/65/EU



REV.	ECN NO OR DESCRIPTION	REVISED	DATE



序号	项目	描述	备注
1	塑胶	LCP	
2	端子	黄铜	
3	焊片	黄铜	
4	盖子	LCP	

## 技术指标:

- 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
- 温度范围:  $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$ .
- 额定电压: 50V, AC.
- 接触电阻:  $\leq 0.02\Omega$ .
- 绝缘电阻:  $\geq 100\text{M}\Omega$ .
- 额定电流:

适用电线型号:  
a. AWG#28:1.0A (per pin)  
b. AWG#30:1.0A (per pin)  
c. AWG#32:0.8A (per pin)

## TABLE:

CSG PART NO.	PIN#	DimA	DimB	DimC
WAFER-NH100L-2A	2PIN	1.00	2.50	4.00
WAFER-NH100L-3A	3PIN	2.00	3.50	5.00
WAFER-NH100L-4A	4PIN	3.00	4.50	6.00
WAFER-NH100L-5A	5PIN	4.00	5.50	7.00
WAFER-NH100L-6A	6PIN	5.00	6.50	8.00
WAFER-NH100L-7A	7PIN	6.00	7.50	9.00
WAFER-NH100L-8A	8PIN	7.00	8.50	10.00
WAFER-NH100L-9A	9PIN	8.00	9.50	11.00
WAFER-NH100L-10A	10PIN	9.00	10.50	12.00
WAFER-NH100L-11A	11PIN	10.00	11.50	13.00
WAFER-NH100L-12A	12PIN	11.00	12.50	14.00
WAFER-NH100L-15A	15PIN	14.00	15.50	17.00

UNLESS OTHERWISE  
SPECIFIED TOLERANCES



东莞市汉博电子科技有限公司  
DONGGUAN HANBO TECHNOLOGY CO., LTD

DECIMALS:	ANGLES:	TITLE	WAFFER 1.0Pitch 立贴带扣SMT
X.X : ±0.25	X.° : ±5°	DWN	xiong WAFER-NH100L-NA
X.XX : ±0.15	X.X° : ±3°	CHKD	lee SCALE:1:1
X.XXX : ±0.05		APVD	wang UNIT: mm
			CUSTOMER COPY
			SIZE: A4 SHEET:10F 1 REV: A4