




Kinghelm®

| REVISIONS |        |             |       |     |      |
|-----------|--------|-------------|-------|-----|------|
| REV       | NUMBER | DESCRIPTION | DWN   | CHK | DATE |
| A         |        | DESIGN      | James |     | 9/26 |
|           |        |             |       |     |      |

NOTES:

1. ELECTRICAL:
- 1.1. VOLTAGE RATING:DCV 300V 10MS
- 1.2. CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
- 1.3. INSULATION RESISTANCE: 5.0M OHM/MIN.
- 1.4. THE CABLE SHOULD BE 100% ELECTRICAL TEST
- 1.5. IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES.
2. MATERIAL:
- 2.1. SEE TABLE
3. ALL COMPONENTS ARE RoHS COMPLIANT.

| ITEM NO. | PART NUMBER | DESCRIPTION         | QTY. |
|----------|-------------|---------------------|------|
| ④        | 套管          | OD:2.5* 15 mm 套管    | 2    |
| ③        | 接头          | SMB公头公针, 直头, 镀金     |      |
| ②        | 接头          | SMB公头公针, 直头, 镀金     | 2    |
| ①        | 同轴线         | RG1.78棕色线, OD:1.8mm | AS   |

深圳市金航标电子有限公司  
SHENZHEN KINGHELM ELECTRON CO., LTD.

|                                                                                       |                                                                         |                 |                                        |             |  |      |              |
|---------------------------------------------------------------------------------------|-------------------------------------------------------------------------|-----------------|----------------------------------------|-------------|--|------|--------------|
| ALL DIMENSION<br>ARE IN MM                                                            | DRAWN James                                                             | DATE 2025-03-10 | TITLE<br><br>KH-SMBJ-SMBJ-RG1.78-100MM |             |  |      |              |
|                                                                                       | CHKD. Frank                                                             | 2025-03-10      |                                        |             |  |      |              |
|                                                                                       | APPD. Scotl                                                             | 2025-03-10      |                                        |             |  |      |              |
|                                                                                       |                                                                         |                 |                                        |             |  |      |              |
| COMPUTER GENERATED<br>IN SOLIDWORKS                                                   |                                                                         |                 | SIZE DWG Number.                       |             |  |      |              |
| DO NOT SCALE<br>THIS DRAWING                                                          |                                                                         |                 | REV A                                  |             |  |      |              |
| PROJECTION                                                                            | GENERAL TOLERANCE FOR<br>ANGLES X.X X.XX X.XXX<br>±1° ±0.3 ±0.25 ±0.150 |                 | B                                      | SCALE: Free |  | TYPE | SHEET 1 OF 1 |
|  |                                                                         |                 |                                        |             |  |      |              |

CUSTOMER P/N: