



RoHS
Compliant
2011/65/EU




REV.	ECN NO OR DESCRIPTION	REVISED	DATE

A

1.00±0.05(PITCH)

N-0.20±0.02




B

DIMC±0.2

DIMB±0.15


DIMA±0.1



C



0.20

1.00



SECTION A-A

序号	项目	描述	备注
1	塑胶	LCP	
2	端子	黄铜	
3	焊片	黄铜	





技术指标:

- 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
- 温度范围: -25° C~85° C.
- 额定电压: 30V, AC/DC.
- 接触电阻: $\leq 0.02\Omega$.
- 绝缘电阻: $\geq 100M\Omega$.
- 额定电流:

适用电线型号:
a. AWG#28:1.0A (per pin)
b. AWG#30:1.0A (per pin)
c. AWG#32:0.8A (per pin)

TABLE:

CSG PART NO.	PIN#	DimA	DimB	DimC
WAFER-NH100W-2A	2PIN	1.00	2.50	4.00
WAFER-NH100W-3A	3PIN	2.00	3.50	5.00
WAFER-NH100W-4A	4PIN	3.00	4.50	6.00
WAFER-NH100W-5A	5PIN	4.00	5.50	7.00
WAFER-NH100W-6A	6PIN	5.00	6.50	8.00
WAFER-NH100W-7A	7PIN	6.00	7.50	9.00
WAFER-NH100W-8A	8PIN	7.00	8.50	10.00
WAFER-NH100W-9A	9PIN	8.00	9.50	11.00
WAFER-NH100W-10A	10PIN	9.00	10.50	12.00
WAFER-NH100W-11A	11PIN	10.00	11.50	13.00
WAFER-NH100W-12A	12PIN	11.00	12.50	14.00
WAFER-NH100W-15A	15PIN	14.00	15.50	17.00



适用线路板

UNLESS OTHERWISE
SPECIFIED TOLERANCES



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

DECIMALS:	ANGLES:	TITLE	Wafer 1.0Pitch 卧贴带扣SMT		
X.X :±0.25	X.° :±5°	DWN	xiong	WAFER-NH100W-NA	
X.XX :±0.15	X.X° :±3°	CHKD	lee	SCALE:1:1	UNIT: mm
X.XXX :±0.05		APVD	wang	SIZE: A4	SHEET:10F 1 REV: A4
				CUSTOMER COPY	