

General Description

The WSK280N06G6 uses advanced technology to provide excellent $R_{DS(ON)}$, low gate charge and operation with gate voltages as low as 10V.

This device is suitable for use as a Battery protection or in other Switching application.

Features

- 100% E_{AS} Guaranteed
- Green Device Available


Product Summary

BV_{DSS}	$R_{DS(ON)}$	I_D
60V	2.1m Ω	280A

Applications

- Battery protection
- UPS

TO-263-6L Pin Configuration



Absolute Maximum Ratings ($T_C=25^\circ\text{C}$, Unless Otherwise Noted)

Symbol	Parameter	Rating	Units
V_{DS}	Drain-Source Voltage	60	V
V_{GS}	Gate-Source Voltage	± 20	
$I_D@T_C=25^\circ\text{C}$	Continuous Drain Current ^{1,6}	280	A
$I_D@T_C=100^\circ\text{C}$	Continuous Drain Current ^{1,6}	248	
I_{DM}	Pulsed Drain Current ²	240	
E_{AS}	Single Pulse Avalanche Energy ³	101	mJ
I_{AS}	Avalanche Current	55	A
$P_D@T_C=25^\circ\text{C}$	Total Power Dissipation ⁴	168	W
T_{STG}	Storage Temperature Range	-55 to 150	$^\circ\text{C}$
T_J	Operating Junction Temperature Range	-55 to 150	

Thermal Data

Symbol	Parameter	Rating	Units
$R_{\theta JA}$	Thermal Resistance Junction-Ambient ¹	0.89	$^\circ\text{C/W}$
$R_{\theta JC}$	Thermal Resistance Junction-Case ¹	1.5	

Electrical Characteristics ($T_J=25^{\circ}\text{C}$, Unless Otherwise Noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Units
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS}=0V$, $I_D=250\mu A$	60	---	---	V
$R_{DS(ON)}$	Static Drain-Source On-Resistance ⁴	$V_{GS}=10V$, $I_D=20A$	---	2.1	3.2	m Ω
$V_{GS(th)}$	Gate Threshold Voltage	$V_{GS}=V_{DS}$, $I_D=250\mu A$	2.0	2.8	4.0	V
I_{DSS}	Drain-Source Leakage Current	$V_{DS}=60V$, $V_{GS}=0V$, $T_J=25^{\circ}\text{C}$	---	---	1.0	μA
		$V_{DS}=60V$, $V_{GS}=0V$, $T_J=100^{\circ}\text{C}$	---	---	100	
I_{GSS}	Gate-Body Leakage Current	$V_{GS}=\pm 20V$, $V_{DS}=0V$	---	---	± 100	nA
g_{fs}	Forward Transconductance ⁴	$V_{DS}=5V$, $I_D=20A$	---	78	---	S
R_g	Gate Resistance	$f=1.0\text{MHz}$	---	2.2	---	Ω
Q_g	Total Gate Charge	$V_{DS}=30V$, $V_{GS}=10V$, $I_D=20A$	---	72.5	---	nC
Q_{gs}	Gate-Source Charge		---	19.5	---	
Q_{gd}	Gate-Drain Charge		---	14	---	
$T_{d(on)}$	Turn-on Delay Time	$V_{DD}=30V$, $V_{GS}=10V$, $R_G=3\Omega$, $I_D=20A$	---	26.5	---	ns
T_r	Rise Time		---	15	---	
$T_{d(off)}$	Turn-off Delay Time		---	73	---	
T_f	Fall Time		---	18	---	
C_{iss}	Input Capacitance	$V_{DS}=30V$, $V_{GS}=0V$, $f=1.0\text{MHz}$	---	5245	---	pF
C_{oss}	Output Capacitance		---	1090	---	
C_{rss}	Reverse Transfer Capacitance		---	25	---	

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Units
I_S	Continuous Source Current	$T_C=25^{\circ}\text{C}$	---	---	125	A
V_{SD}	Diode Forward Voltage ⁴	$I_S=20A$, $V_{GS}=0V$	---	---	1.2	V
t_{rr}	Reverse Recovery Time	$I_F=20A$, $di/dt=100A/\mu s$	---	25	---	ns
Q_{rr}	Reverse Recovery Charge		---	90	---	nC

Note:

1. The data tested by surface mounted on a 1 inch² FR-4 board with 2OZ copper.
2. The data tested by pulsed, pulse width. The E_{AS} data shows Max. rating.
3. The power dissipation is limited by 150°C junction temperature.
4. E_{AS} condition: $T_J=25^{\circ}\text{C}$, $V_{DD}=48V$, $V_{GS}=10V$, $R_G=25\Omega$, $L=0.1\text{mH}$, $I_{AS}=55A$
5. The data is theoretically the same as I_D and I_{DM} , in real applications, should be limited by total power dissipation.

Typical Characteristics




Figure 1. Output Characteristics




Figure 3. Forward Characteristics of Reverse




Figure 2. Transfer Characteristics




Figure 4. $R_{DS(ON)}$ vs. V_{GS}




Figure 5. $R_{DS(ON)}$ vs. I_D










Figure 6. Normalized $R_{DS(on)}$ vs. Temperature

Typical Characteristics (Cont.)

Figure 7. Capacitance Characteristics

Figure 8. Gate Charge Characteristics

Figure 9. Power Dissipation

Figure 10. Safe Operating Area

Figure 11. Normalized Maximum Transient Thermal Impedance

Packaging information



SYMBOL	MILLIMETERS		INCHES	
	MIN.	MAX.	MIN.	MAX.
A	4.25	4.55	0.167	0.179
A1	0.01	0.25	0.000	0.010
b	0.50	0.70	0.020	0.028
b1	0.60	0.84	0.024	0.033
c	0.40	0.60	0.016	0.024
c1	1.20	1.40	0.047	0.055
D	9.05	9.45	0.356	0.372
D1	6.90	9.00	0.272	0.354
E	9.80	10.20	0.386	0.402
E1	7.25	9.00	0.285	0.354
e	1.27 BSC		0.05 BSC	
H	14.65	15.35	0.577	0.604
L	2.40	3.00	0.094	0.118
L1	0.80	1.20	0.031	0.047
L2	0.85	1.15	0.330	0.045
θ	2°	8°	2°	8°

Attention

- 1, Any and all Winsok power products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your Winsok power representative nearest you before using any Winsok power products described or contained herein in such applications.
- 2, Winsok power assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all Winsok power products described or contained herein.
- 3, Specifications of any and all Winsok power products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate, and test devices mounted in the customer's products or equipment.
- 4, Winsok power Semiconductor CO., LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- 5, In the event that any or all Winsok power products(including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.
- 6, No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of Winsok power Semiconductor CO., LTD.
- 7, Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production. Winsok power believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.
- 8, Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the Winsok power product that you intend to use.
- 9, this catalog provides information as of Sep.2014. Specifications and information herein are subject to change without notice.