




REV.	ECN NO OR DESCRIPTION	REVISED	DATE



SPECIFICATION NOTES:

ELECTRICAL:



1. VOLTAGE RATING: 125 VAC RMS
2. CURRENT RATING: 1.5 AMP
3. CONTACT RESISTANCE: 30mΩ MAX.
4. INSULATION RESISTANCE: 500MΩMIN. AT 500V DC.
5. DIELECTRIC STRENGTH: 1000 VAC 50Hz 1MINUTE

MECHANICAL:

- 1.HOUSING MATERIAL:
SEE PART NUMBER.
2. CONTACTS:Ø0.46mm PHOSPHOR BRONZE,GOLD
PLATING OVER NICKEL
- 3.SHIELD:0.20mm THICKNESS COPPER ALLOY WITH
NICKEL PLATED.
4. OPERATING LIFE:750 CYCLES MIN.
5. MATING FORCE: 22N MAX.
UNMATING FORCE: 22N MAX.
6. Wave soldering Temp.: 235°+/-5°

ENVIRONMENTAL:

1. STORAGE:-40°C TO +85°C
2. OPERATION: -40°C TO +85°C



Recommend PCB Layout
TOLERANCES:±0.05

UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS: ANGLES:
X :±0.35 X :±2°
X.X :±0.25 X.X :±1°
X.XX :±0.15



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE	RJ45 5224 8P8C 全包无灯 脚3.85			
DWN	xiong	PART NO.	RJ45-5211881B16-A	
CHKD	lee	SCALE:1:1	UNIT: mm	
APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4

CUSTOMER COPY