








REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

Part No	Pin	A	B
A396E1L1-2H2P12	2	3.96	7.92
A396E1L1-2H3P12	3	7.92	11.88
A396E1L1-2H4P12	4	11.88	15.84
A396E1L1-2H5P12	5	15.84	19.80
A396E1L1-2H6P12	6	19.80	23.76
A396E1L1-2H7P12	7	23.76	27.72
A396E1L1-2H8P12	8	27.72	31.68
A396E1L1-2H9P12	9	31.68	35.64
A396E1L1-2H10P12	10	35.64	39.60
A396E1L1-2H11P12	11	39.60	43.56
A396E1L1-2H12P12	12	43.56	47.52
A396E1L1-2H13P12	13	47.52	51.48
A396E1L1-2H14P12	14	51.48	55.44
A396E1L1-2H15P12	15	55.44	59.40
A396E1L1-2H16P12	16	59.40	63.36



序号	品名	材质
1	VH3.96 胶芯	PA66 UL94V-2 Yellow
2	VH3.96 直针 端子	Copper Alloy/ Tin Plating

Technical Index:
1. Temperature range: -25°C~85°C.
2. Rated voltage: 250V DC/AC(rms).
3. Rated current: 7.0A.
4. Contact resistance: ≤20mΩ.
5. Withstanding voltage: 1500V AC/minute.
6. Insulation resistance: ≥1000MΩ.

适用线路板(PCB LAYOUT)

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.X:±0.35	X.X':±3"	PART NO. A396E1L1-2HXP12	TITLE: Socket-type terminal Vertical plug		
X.XX:±0.25	X.XX':±2"				
X.XXX:±0.15					
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG		
MATERILA	— — —	CHED: Olvia			
FINISH	— — —	APPD: Ava		SCALE	SHEET
				N:A	1/1