




**TO-220F Plastic-Encapsulate Transistors****3DA4793** TRANSISTOR (NPN)**FEATURES**

- Complementary to 3CA1837
- Collector Power Dissipation
 $P_{CM} : 2W (T_a=25.)$
20 W ($T_c=25.$)

**MARKING**

3DA4793=Device code
Solid dot=Green mold compound device,
if none, the normal device
XXXX=Code








Equivalent Circuit**MAXIMUM RATINGS ($T_a=25^\circ\text{C}$ unless otherwise noted)**

Symbol	Parameter	Value	Unit
V_{CBO}	Collector-Base Voltage	230	V
V_{CEO}	Collector-Emitter Voltage	230	V
V_{EBO}	Emitter-Base Voltage	5	V
I_C	Collector Current -Continuous	1000	mA
P_C	Collector Power Dissipation	1.5	W
T_J, T_{stg}	Operation Junction and Storage Temperature Range	-55-150	$^\circ\text{C}$


ELECTRICAL CHARACTERISTICS (T_a=25°C unless otherwise specified)

Parameter	Symbol	Test conditions	Min	Typ	Max	Unit
Collector-base breakdown voltage	V _{(BR)CBO}	I _C =0.1mA, I _E =0	230			V
Collector-emitter breakdown voltage	V _{(BR)CEO}	I _C =1mA, I _B =0	230			V
Emitter-base breakdown voltage	V _{(BR)EBO}	I _E =100μA, I _C =0	5			V
Collector cut-off current	I _{CBO}	V _{CB} =230V, I _E =0			10	μA
Emitter cut-off current	I _{EBO}	V _{EB} =5V, I _C =0			10	μA
DC current gain	h _{FE}	V _{CE} =5V, I _C =100mA	100		320	
Collector-emitter saturation voltage	V _{CE(sat)}	I _C =500mA, I _B =50mA			1.5	V
Transition frequency	f _T	V _{CE} =10V, I _C =100mA	30			MHz

Typical Characteristics



TO-220F Package Outline Dimensions



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	4.300	4.700	0.169	0.185
A1	1.300 REF.		0.051 REF.	
A2	2.800	3.200	0.110	0.126
A3	2.500	2.900	0.098	0.114
b	0.500	0.750	0.020	0.030
b1	1.100	1.350	0.043	0.053
b2	1.500	1.750	0.059	0.069
c	0.500	0.750	0.020	0.030
D	9.960	10.360	0.392	0.408
E	14.800	15.200	0.583	0.598
e	2.540 TYP.		0.100 TYP.	
F	2.700 REF.		0.106 REF.	
Φ	3.300	3.700	0.130	0.146
L	28.000	28.400	1.102	1.118
L1	1.700	1.900	0.067	0.075
L2	0.900	1.100	0.035	0.043