



TRANSISTOR (NPN)

MARKING:




Equivalent Circuit:



SOT-23

1.BASE
2.EMITTER
3.COLLECTOR



FEATURES:

※ High Current Gain

MAXIMUM RATINGS (Ta=25°C unless otherwise noted)


Parameter	Symbol	Value	Unit
Collector-Base Voltage	VCBO	80	V
Collector-Emitter Voltage	VCEO	80	V
Emitter-Base Voltage	VEBO	12	V
Collector Current	IC	500	mA
Collector Power Dissipation	PC	200	mW
Thermal Resistance From Junction To Ambient	RθJA	625	°C/W
Junction Temperature	Tj	150	°C
Storage Temperature	Tstg	-55~+150	°C

ELECTRICAL CHARACTERISTICS (Ta=25°C unless otherwise specified)


Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Collector-base breakdown voltage	V(BR)CBO	IC= 100μA, IE=0	80			V
Collector-emitter breakdown voltage	V(BR)CEO	IC= 100μA, VBE=0	80			V
Emitter-base breakdown voltage	V(BR)EBO	IE=10μA, IC=0	12			V
Collector cut-off current	ICBO	VCB=60 V , IE=0			0.1	μA
Collector cut-off current	ICEO	VCB=60V , VBE=0			0.5	μA
Emitter cut-off current	IEBO	VEB= 10V , IC=0			0.1	μA
DC current gain	hFE	VCE=5V, IC= 10mA	10			K
	hFE	VCE=5V, IC= 100mA	10			K
Collector-emitter saturation voltage	VCE(sat)	IC=10mA, IB= 0.01mA			1.2	V
Base-emitter saturation voltage	VBE(sat)	IC=100 mA, VCE=5V			2	V
Transition frequency	fT	VCE=5V, IC= 10mA f=100MHz	125			MHz
Collector output capacitance	Cob	VCB=1V, IE=0, f=1MHz			8	pF

Pulse test: pulse width ≤300μs, duty cycle ≤ 2.0%.

TYPICAL ELECTRICAL AND THERMAL CHARACTERISTICS



SOT-23 PACKAGE OUTLINE DIMENSIONS



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	0.900	1.150	0.035	0.045
A1	0.000	0.100	0.000	0.004
A2	0.900	1.050	0.035	0.041
b	0.300	0.500	0.012	0.020
c	0.080	0.150	0.003	0.006
D	2.800	3.000	0.110	0.118
E	1.200	1.400	0.047	0.055
E1	2.250	2.550	0.089	0.100
e	0.95TYP		0.037TYP	
e1	1.800	2.000	0.071	0.079
L	0.550 REF		0.022 REF	
L1	0.300	0.500	0.012	0.020
θ	0°	8°	0°	8°