

Silicon Carbide Power MOSFET N-Channel Enhancement Mode

Features



- High Blocking Voltage with Low On-Resistance
- High Speed Switching with Low Capacitances
- Easy to Parallel and Simple to Drive
- Avalanche Ruggedness
- Halogen Free, RoHS Compliant

Typical Applications

- Solar inverters
- Switch Mode Power Supplies
- High voltage DC/DC converters
- Battery Chargers
- Motor Drives
- Pulsed Power applications

Benefits

- Higher System Efficiency
- Reduced Cooling Requirements
- Increased Power Density
- Increase system switching frequency



ORDERING INFORMATION

HT36N1200AKZ

$T_A = -55^\circ$ to 150° C for all packages

Key Parameters

Parameter	Symbol	Min.	Typ.	Max	Unit	Conditions	Note
Drain - Source Voltage	V_{DS}			1200	V	$T_c = 25^\circ\text{C}$	
Maximum Gate - Source Voltage	$V_{GS(max)}$	-10		+25		Transient	
Operational Gate-Source Voltage	$V_{GS op}$		-5/20			Static	Note 1
DC Continuous Drain Current	I_D			36	A	$V_{GS} = 20\text{ V}, T_c = 25^\circ\text{C}, T_J \leq 150^\circ\text{C}$	Fig. 19 Note 2
				26		$V_{GS} = 20\text{ V}, T_c = 100^\circ\text{C}, T_J \leq 150^\circ\text{C}$	
Pulsed Drain Current	I_{DM}			160		t_{pmax} limited by T_{Jmax} $V_{GS} = 20\text{ V}, T_c = 25^\circ\text{C}$	Fig. 22
Power Dissipation	P_D			192	W	$T_c = 25^\circ\text{C}, T_J = 150^\circ\text{C}$	Fig. 20
Operating Junction and Storage Temperature	T_J, T_{stg}			-55 to +150	$^\circ\text{C}$		
Solder Temperature	T_L			260		According to JEDEC J-STD-020	
Mounting Torque	M_D			1 8.8	Nm lbf-in	M3 or 6-32 screw	

Note (1): Recommended turn-on gate voltage is 20V with $\pm 5\%$ regulation tolerance, see Application Note PRD-04814 for additional details
 Note (2): Verified by design

Electrical Characteristics ($T_C = 25^\circ\text{C}$ unless otherwise specified)

Parameter	Symbol	Min.	Typ.	Max.	Unit	Test Conditions	Note
Drain-Source Breakdown Voltage	$V_{(BR)DSS}$	1200	—	—	V	$V_{GS} = 0\text{ V}, I_D = 100\text{ }\mu\text{A}$	Fig. 11
Gate Threshold Voltage	$V_{GS(th)}$	2.0	2.9	4		$V_{DS} = V_{GS}, I_D = 5\text{ mA}$	
		—	2.4	—		$V_{DS} = V_{GS}, I_D = 5\text{ mA}, T_J = 150^\circ\text{C}$	
Zero Gate Voltage Drain Current	I_{DSS}	—	1	100	μA	$V_{DS} = 1200\text{ V}, V_{GS} = 0\text{ V}$	
Gate-Source Leakage Current	I_{GSS}	—	—	250	nA	$V_{GS} = 20\text{ V}, V_{DS} = 0\text{ V}$	
Drain-Source On-State Resistance	$R_{DS(on)}$	—	80	98	m Ω	$V_{GS} = 20\text{ V}, I_D = 20\text{ A}$	Fig. 4, 5, 6
		—	144	—		$V_{GS} = 20\text{ V}, I_D = 20\text{ A}, T_J = 150^\circ\text{C}$	
Transconductance	g_{fs}	—	10	—	S	$V_{DS} = 20\text{ V}, I_{DS} = 20\text{ A}$	Fig. 7
		—	9	—		$V_{DS} = 20\text{ V}, I_{DS} = 20\text{ A}, T_J = 150^\circ\text{C}$	
Input Capacitance	C_{iss}	—	1130	—	pF	$V_{GS} = 0\text{ V}$	Fig. 17, 18
Output Capacitance	C_{oss}	—	92	—		$V_{DS} = 1000\text{ V}$	
Reverse Transfer Capacitance	C_{rss}	—	7.5	—		$f = 1\text{ MHz}$	
C_{oss} Stored Energy	E_{oss}	—	50	—	μJ	$V_{AC} = 25\text{ mV}$	Fig. 16
Avalanche Energy, Single Pluse	E_{AS}	—	1	—	J	$I_D = 20\text{ A}, V_{DD} = 50\text{ V}$	Fig. 29
Turn-On Switching Energy	E_{on}	—	523	—	μJ	$V_{DS} = 800\text{ V}, V_{GS} = -5\text{ V}/20\text{ V},$ $I_D = 20\text{ A}, R_{G(ext)} = 2.5\text{ }\Omega, L = 156\text{ }\mu\text{H}$	Fig. 25
Turn-Off Switching Energy	E_{off}	—	72	—			
Turn-On Delay Time	$t_{d(on)}$	—	15	—	ns	$V_{DD} = 800\text{ V}, V_{GS} = -5\text{ V}/20\text{ V}$ $I_D = 20\text{ A}, R_{G(ext)} = 2.5\text{ }\Omega, R_L = 40\text{ }\Omega,$ Timing relative to V_{DS} Per IEC60747-8-4 pg 83	Fig. 27
Rise Time	t_r	—	22	—			
Turn-Off Delay Time	$t_{d(off)}$	—	24	—			
Fall Time	t_f	—	14	—			
Internal Gate Resistance	$R_{G(int)}$	—	3.9	—	Ω	$f = 1\text{ MHz}, V_{AC} = 25\text{ mV}$	
Gate to Source Charge	Q_{gs}	—	17	—	nC	$V_{DS} = 800\text{ V}, V_{GS} = -5/20\text{ V}$ $I_D = 20\text{ A}$ Per IEC60747-8-4 pg 21	Fig. 12
Gate to Drain Charge	Q_{gd}	—	29	—			
Total Gate Charge	Q_g	—	71	—			

Reverse Diode Characteristics

Parameter	Symbol	Typ.	Max.	Unit	Test Conditions	Notes
Diode Forward Voltage	V_{SD}	4.3	—	V	$V_{GS} = -5\text{ V}, I_{SD} = 10\text{ A}$	Fig. 8, 9, 10
Diode Forward Voltage		3.8	—		$V_{GS} = -5\text{ V}, I_{SD} = 10\text{ A}, T_J = 150^\circ\text{C}$	
Continuous Diode Forward Current ¹	I_S	—	36	A	$T_C = 25^\circ\text{C}$	Note 1
Reverse Recovery Time ¹	t_{rr}	14	—	ns	$V_{GS} = -5\text{ V}, I_{SD} = 20\text{ A}, V_R = 800\text{ V}$ $di_f/dt = 1950\text{ A}/\mu\text{s}$	Note 1
Reverse Recovery Charge ¹	Q_{rr}	78	—	nC		
Peak Reverse Recovery Current ¹	I_{RRM}	14	—	A		

Note:

¹ When using SiC Body Diode the maximum recommended $V_{GS} = -5\text{ V}$
Thermal Characteristics

Parameter	Symbol	Typ	Max.	Unit	Note
Thermal Resistance from Junction to Case	$R_{\theta JC}$	0.60	0.65	$^\circ\text{C}/\text{W}$	Fig. 21
Thermal Resistance From Junction to Ambient	$R_{\theta JA}$	—	40		

Typical Performance




Figure 1. Output Characteristics $T_j = -55^\circ\text{C}$




Figure 2. Output Characteristics $T_j = 25^\circ\text{C}$




Figure 3. Output Characteristics $T_j = 150^\circ\text{C}$




Figure 4. Normalized On-Resistance vs. Temperature




Figure 5. On-Resistance vs. Drain Current
For Various Temperatures




Figure 6. On-Resistance vs. Temperature
For Various Gate Voltage

Typical Performance




Figure 7. Transfer Characteristic For Various Junction Temperatures




Figure 8. Body Diode Characteristic at -55°C




Figure 9. Body Diode Characteristic at 25°C




Figure 10. Body Diode Characteristic at 150°C




Figure 11. Threshold Voltage vs. Temperature




Figure 12. Gate Charge Characteristics

Typical Performance




Figure 13. 3rd Quadrant Characteristic at -55°C




Figure 14. 3rd Quadrant Characteristic at 25°C




Figure 15. 3rd Quadrant Characteristic at 150°C




Figure 16. Output Capacitor Stored Energy




Figure 17. Capacitances vs. Drain-Source Voltage (0 - 200 V)




Figure 18. Capacitances vs. Drain-Source Voltage (0 - 1000 V)

Typical Performance




Figure 19. Continuous Drain Current Derating vs. Case Temperature




Figure 20. Maximum Power Dissipation Derating vs. Case Temperature




Figure 21. Transient Thermal Impedance (Junction - Case)




Figure 22. Safe Operating Area




Figure 23. Clamped Inductive Switching Energy vs. Drain Current ($V_{DD} = 600\text{ V}$)




Figure 24. Clamped Inductive Switching Energy vs. Drain Current ($V_{DD} = 800\text{ V}$)

Typical Performance




Figure 25. Clamped Inductive Switching Energy vs $R_{G(\text{ext})}$




Figure 26. Clamped Inductive Switching Energy vs. Temperature




Figure 27. Switching Times vs. $R_{G(\text{ext})}$




Figure 28. Switching Times Definition




Figure 29. Single Avalanche SOA curve

Test Circuit Schematic





Figure 31. Body Diode Recovery Test Circuit

Package Dimensions


SYMBOL	MIN (mm)	MAX (mm)
A	4.83	5.21
A1	2.23	2.54
A2	1.91	2.16
b	1.07	1.33
b1	2.39	2.94
b3	1.07	1.60
b7	1.30	1.70
b8	1.80	2.20
c	0.55	0.68
D	23.30	23.63
D1	16.25	17.65
D2	5.55	5.95
E	15.75	16.13
E1	13.1	14.15
E2	3.68	5.10
E3	1.00	1.90
E4	12.38	13.43
E5	14.65	15.05
e1	5.08 BSC	
L	17.31	17.82
L1	3.97	4.37
L2	2.35	2.65
ϕP	3.51	3.65
Q	5.49	6.00
S	6.04	6.30
T	17.5° REF.	
W	3.5° REF.	
X	4° REF.	

1	DRAIN
2	SOURCE
3	DRIVER SOURCE
4	GATE
5	DRAIN

NOTE:

- ALL METAL SURFACES ARE TIN PLATED (MATTE), EXCEPT AREA OF CUT.
- DIMENSIONING & TOLERANCING CONFORM TO ASME Y14.5M-1994.
- ALL DIMENSIONS ARE LISTED IN MILLIMETERS. ANGLES ARE IN DEGREES.
- BURR OR MOLD FLASH SIZE (0.5 mm) IS NOT INCLUDED IN THE DIMENSIONS

Recommended Solder Pad Layout

