

NOTES

MATERIAL

1.HOUSING MATERIAL : GLASS FILLED POLYESTER UL94V-0.
2.CONTACT MATERIAL : PHOSPHOR BRONZE $\phi 0.46\text{mm}$.
3.PLATING : GOLD LATING OVER NICKEL.

ELECTRICAL



1.VOLTAGE RATING : 125 VAC RMS.
2.CURRENT RATING : 1.5 AMP.
3.CONTACT RESISTANCE : 40 MILLIOHMS MAX.
4.INSULATION RESISTANCE : 500 MEGOHMS MIN @ 100V DC .
5.DIELECTRIC DIELECTRIC RESISTANCE : 500V DC RMS 50Hz. 1MIN.

MECHANICAL

1.DURRABILITY : 750 CYCLES MIN.
2.MATING/UNMATING FORCE: 2.24 KG.F MAX.

ENVIRONMENTAL:

1.STORAGE : $-40^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
2.OPERATION : $-40^{\circ}\text{C}\sim+85^{\circ}\text{C}$.



PART NUMBER DESCRIPTION:

RJ45-306-005-XX

类别码

5621 1X1

流水码

18:全塑2.8脚-0.5u"淡 PBT黑盘装

8	—
7	—
6	RX-
5	—
4	—
3	RX+
2	TX-
1	TX+
PIN序	说明

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			
DECIMALS:	ANGLES:	TITLE: 5621 1X1全塑DIP 2.8脚 0.5u"淡 PBT黑	
.X:±0.35	X":±3'	PAR	RJ45-306-005-18
.XX:±0.25	.X":±2'	DWN	
.XXX:±0.15	.XX":±1'	CHKD	
CUSTOMER COPY		APVD	
		SCALE:1:1	UNIT:MM
		SIZE:A4	SHEET:1F1
			REV:A