


1. Compatible with various 10/100 Base-TX transceiver requiring 1:1 transmit and receive turns ratio
2. Compliant with IEEE 802.3at standard including baseline wander compensation specification of  $350\mu\text{H}$  OCL when Biased at 8mA
3. Low profile Surface Mount Packaging designed for Hi-Temp Reflow Process
4. Single channel interface for 10/100Mbps Ethernet applications with CMC's tuned to Enhance EMC system performance
5. Operating Temperature range:  $-0^{\circ}\text{C}$  TO  $+70^{\circ}\text{C}$
6. Storage temperature range:  $-25^{\circ}\text{C}$  TO  $+125^{\circ}\text{C}$



## DIMENSIONS & SCHEMATICS




**Note:** 1. Dimension: mm, 2. Unless otherwise specified, tolerances are:  $\pm 0.15\text{mm}$

## TECHNICAL SPECIFICATIONS

OCL :	350 $\mu\text{H}$ Min. @ 100 KHz, 100mV with 8mA DC Bias
Leakage	0.5 $\mu\text{H}$ Max. @ 100KHz, 0.1V
Inductance: Cw/w:	28pF Max. @ 100KHz, 0.1V
DCR:	1.20 $\Omega$ Max.
Turns Ratio( $\pm 5\%$ ):	1CT:1CT(TX), 1CT:1CT(RX)
Polarity:	1-16, 6-11 In-Phase
Insertion Loss:	-1.1 dB Max. @ 1-100MHz
Return Loss:	-16dB Min. @ 1-30MHz -12 dB Min. @ 30-60 MHz -10 dB Min. @ 60-80 MHz
Cross Talk:	-42 dB Min. @ 1-60 MHz -35 dB Min. @ 60-100 MHz
Common Mode Rejection :	-42 dB Min. @ 1-30 MHz -35 dB Min. @ 60 MHz -30 dB Min. @ 80-100 MHz
Isolation HI-POT:	1500Vms 1mA 1Second

## PACKING SPECIFICATION



1. units/reel: 750PCS
2. reel/carton: 7PCS
3. units/carton : 5250PCS

EXPORT CARTON: 367(L)x337(W)x235(H)