




技术特性/Specifications:

额定电压 Rated voltage: 50V AC, DC

额定电流 Rated current: 0.7A AC, DC

接触电阻 Contact resistance: 20m Ω max

绝缘电阻 Insulation resistance: 500M Ω min

耐压 Withstand voltage: 500V AC/minute

环境温度 Ambient temperature: -40 $^{\circ}$ C~+105 $^{\circ}$ C

适用线规 Wire range: AWG#30~#26





REV.	REVISION DESCRIPTION	DATE	APPD

NOTES

Available in 02 through 15 Circuits.

Material:Nylon UL94V-0 (2) .

Accepts DL15002-T Crimp Terminal.



Circuits	Type	Dimension mm		Circuits	Type	Dimension mm	
		A	B			A	B
2	SZN-2Y	1.50	3.70	9	SZN-9Y	12.00	14.20
3	SZN-3Y	3.00	5.20	10	SZN-10Y	13.50	15.70
4	SZN-4Y	4.50	6.70	11	SZN-11Y	15.00	17.20
5	SZN-5Y	6.00	8.20	12	SZN-12Y	16.50	18.70
6	SZN-6Y	7.50	9.70	13	SZN-13Y	18.00	20.20
7	SZN-7Y	9.00	11.20	14	SZN-14Y	19.50	21.70
8	SZN-8Y	10.50	12.70	15	SZN-15Y	21.00	23.20

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD			
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: DL15002 (SZN)-Y		TITLE: 1.50 mm Pitch Housing	
.XX: ± 0.15	.X° : ± 2.0°	DR:Chen Quan Long	DATE:22/08/01	PART NO:	
.XXX: ± 0.01	.XX° : ± 1.0°			SCALE: N/A	PAGE: 1/1
FINISH: _____		CHKD:Wu Hui	DATE:22/08/01	UNITS: mm	REV. : A
DRAWING NO:		APPD:Ren An De	DATE:22/08/01		

A

B

C

D

E

F

A




B

C


D

E


F



SECTION A-A



SECTION B-B



SECTION C-C

NOTES

Used in DL15002-Y Series Housing.

Material : Phosphor Bronze .

Finish: Tin plated.

Thickness: 0.2 mm.

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO .,LTD			
. X: ± 0.25	X° : ± 3.0°	PRODUCT NAME:		TITLE:	
. XX: ± 0.15	. X° : ± 2.0°	DL15002 (SZN) -T		1.5mm Pitch CrimpTerminal	
. XXX: ± 0.01	. XX° : ± 1.0°	DR:Chen Quan Long	DATE:22/08/01	PART NO:	
FINISH:		CHKD:Wu Hui	DATE:22/08/01	SCALE: N/A	PAGE: 1/1
DRAWING NO:		APPD:Ren An De	DATE:22/08/01	UNITS: mm	REV.: A