



2P	Holder+Pillar
3P	Holder+Holder+Pillar
4P	Holder+Pillar+Holder+Pillar
5P	Holder+Pillar+Pillar+Holder+Pillar
5P over	Holder+Pillar+ ^{pillar} ...+Pillar+Holder+Pillar

DIM		TOL			
		2P-4P	5P-8P	9P-12P	13P-16P
Dim L	N×7.5-2.5	±0.15	±0.25	±0.30	±0.40
Dim P	(N-1)×7.5	±0.15	±0.25	±0.30	±0.40
Dim B	N×7.5+0.7	±0.15	±0.25	±0.30	±0.40

HI xx 2 1 x 2 xxxx G

No. OF POLES ————
02: 2 POLES
:
:
16: 16 POLES

COLOR ————
0: BLACK (RAL 9005)
5: GREEN (RAL 6018/T)
6: BLUE (RAL 5015/A)
8: GREY (RAL 7035/D)

————— G: Pb<40000ppm
0000: Standard
Any special item by
customer request.
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		HI 7.5mm -With Flange 100% protected against mismatching					
PART NO.		Hlxx21x2xxxxG			DWG NO.		8HI0702
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
			Dacheng 2012.08.14		UNIT: mm		X. ±0.50
					SCALE: NONE		X.X ±0.30
					SHFFT: 01/01 RFV: C		X.XX ±0.10 X° +1°