

STARTER, 3RE41215AA154TB0, WITH MODS



|                                                                          |                                 |
|--------------------------------------------------------------------------|---------------------------------|
| product brand name                                                       | Siemens                         |
| product designation                                                      | Non-reversing motor starter     |
| special product feature                                                  | Start-Stop Push Buttons         |
| <b>General technical data</b>                                            |                                 |
| weight [lb]                                                              | 8 lb                            |
| Height x Width x Depth [in]                                              | 11 × 7 × 5 in                   |
| touch protection against electrical shock                                | NA for enclosed products        |
| installation altitude [ft] at height above sea level maximum             | 6 560 ft                        |
| ambient temperature [°F] during storage                                  | -22 ... +149 °F                 |
| ambient temperature [°F] during operation                                | -4 ... +104 °F                  |
| ambient temperature during storage                                       | -30 ... +65 °C                  |
| ambient temperature during operation                                     | -20 ... +40 °C                  |
| country of origin                                                        | Germany                         |
| <b>Power and control electronics</b>                                     |                                 |
| number of poles for main current circuit                                 | 3                               |
| type of voltage of the control supply voltage                            | AC                              |
| control supply voltage                                                   |                                 |
| • at AC at 50 Hz rated value                                             | 24 V                            |
| • at AC at 60 Hz rated value                                             | 24 V                            |
| disconnecter functionality                                               | No                              |
| yielded mechanical performance [hp] for 3-phase AC motor                 |                                 |
| • at 200/208 V rated value                                               | 1.5 hp                          |
| • at 220/230 V rated value                                               | 2 hp                            |
| • at 460/480 V rated value                                               | 3 hp                            |
| • at 575/600 V rated value                                               | 5 hp                            |
| <b>Contactor</b>                                                         |                                 |
| number of NO contacts for main contacts                                  | 3                               |
| operating voltage at AC-3 rated value maximum                            | 600 V                           |
| mechanical service life (operating cycles) of the main contacts typical  | 30 000 000                      |
| <b>Auxiliary contact</b>                                                 |                                 |
| number of NC contacts for auxiliary contacts                             | 0                               |
| number of NO contacts for auxiliary contacts                             | 1                               |
| number of total auxiliary contacts maximum                               | 6                               |
| contact rating of auxiliary contacts of contactor according to UL        | 10A@600V(A600), 2.5A@600V(Q600) |
| <b>Coil</b>                                                              |                                 |
| apparent pick-up power of magnet coil at AC                              | 26.4 VA                         |
| apparent holding power of magnet coil at AC                              | 4.4 VA                          |
| operating range factor control supply voltage rated value of magnet coil | 0.8 ... 1.1                     |
| ON-delay time                                                            | 9 ... 35 ms                     |

|                                                                                                                               |                                       |
|-------------------------------------------------------------------------------------------------------------------------------|---------------------------------------|
| OFF-delay time                                                                                                                | 3.5 ... 14 ms                         |
| <b>Overload relay</b>                                                                                                         |                                       |
| product function                                                                                                              |                                       |
| • overload protection                                                                                                         | Yes                                   |
| • phase failure detection                                                                                                     | Yes                                   |
| • asymmetry detection                                                                                                         | Yes                                   |
| • ground fault detection                                                                                                      | Yes                                   |
| • test function                                                                                                               | Yes                                   |
| • external reset                                                                                                              | Yes                                   |
| reset function                                                                                                                | Manual, automatic and remote          |
| trip class                                                                                                                    | CLASS 5 / 10 / 20 / 30                |
| adjustment range of thermal overload trip unit                                                                                | 4 ... 16                              |
| number of NC contacts of auxiliary contacts of overload relay                                                                 | 1                                     |
| number of NO contacts of auxiliary contacts of overload relay                                                                 | 1                                     |
| operational current of auxiliary contacts of overload relay                                                                   |                                       |
| • at AC at 600 V                                                                                                              | 5 A                                   |
| • at DC at 250 V                                                                                                              | 1 A                                   |
| contact rating of auxiliary contacts of overload relay according to UL                                                        | 5A@600VAC (B600), 1A@250VDC (R300)    |
| insulation voltage (Ui)                                                                                                       |                                       |
| • with single-phase operation at AC rated value                                                                               | 600 V                                 |
| • with multi-phase operation at AC rated value                                                                                | 300 V                                 |
| <b>Enclosure</b>                                                                                                              |                                       |
| degree of protection NEMA rating of the enclosure                                                                             | NEMA 1 standard size enclosure        |
| design of the housing                                                                                                         | indoors, usable on a general basis    |
| <b>Mounting/wiring</b>                                                                                                        |                                       |
| mounting position                                                                                                             | Vertical                              |
| fastening method                                                                                                              | Surface mounting and installation     |
| type of electrical connection for supply voltage line-side                                                                    | Screw-type terminals                  |
| tightening torque [lbf-in] for supply                                                                                         | 7 ... 10 lbf-in                       |
| type of connectable conductor cross-sections at line-side for AWG cables single or multi-stranded                             | 2x (20 ... 16), 2x (18 ... 14), 2x 12 |
| temperature of the conductor for supply maximum permissible                                                                   | 60 °C                                 |
| material of the conductor for supply                                                                                          | CU                                    |
| type of electrical connection for load-side outgoing feeder                                                                   | Screw-type terminals                  |
| tightening torque [lbf-in] for load-side outgoing feeder                                                                      | 7 ... 10 lbf-in                       |
| type of connectable conductor cross-sections for AWG cables for load-side outgoing feeder single or multi-stranded            | 2x (20 ... 16), 2x (18 ... 14), 2x 12 |
| temperature of the conductor for load-side outgoing feeder maximum permissible                                                | 60 °C                                 |
| material of the conductor for load-side outgoing feeder                                                                       | CU                                    |
| type of electrical connection of magnet coil                                                                                  | Screw-type terminals                  |
| tightening torque [lbf-in] at magnet coil                                                                                     | 7 ... 10 lbf-in                       |
| type of connectable conductor cross-sections of magnet coil for AWG cables single or multi-stranded                           | 2x (20 ... 16), 2x (18 ... 14), 2x 12 |
| temperature of the conductor at magnet coil maximum permissible                                                               | 75 °C                                 |
| material of the conductor at magnet coil                                                                                      | CU                                    |
| type of electrical connection for auxiliary contacts                                                                          | Screw-type terminals                  |
| tightening torque [lbf-in] at contactor for auxiliary contacts                                                                | 7 ... 10 lbf-in                       |
| type of connectable conductor cross-sections at contactor for AWG cables for auxiliary contacts single or multi-stranded      | 2x (20 ... 16), 2x (18 ... 14), 2x 12 |
| temperature of the conductor at contactor for auxiliary contacts maximum permissible                                          | 75 °C                                 |
| material of the conductor at contactor for auxiliary contacts                                                                 | CU                                    |
| tightening torque [lbf-in] at overload relay for auxiliary contacts                                                           | 7 ... 10 lbf-in                       |
| type of connectable conductor cross-sections at overload relay for AWG cables for auxiliary contacts single or multi-stranded | 1x (20 ... 14), 2x (20 ... 14)        |
| temperature of the conductor at overload relay for auxiliary contacts maximum permissible                                     | 75 °C                                 |
| material of the conductor at overload relay for auxiliary contacts                                                            | CU                                    |
| <b>Short-circuit current rating</b>                                                                                           |                                       |
| design of the fuse link for short-circuit protection of the main circuit required                                             | Class J                               |

|                                                                                                      |                                  |
|------------------------------------------------------------------------------------------------------|----------------------------------|
| design of the short-circuit trip                                                                     | Thermal magnetic circuit breaker |
| maximum short-circuit current breaking capacity (Icu)                                                |                                  |
| <ul style="list-style-type: none"> <li>• at 240 V</li> <li>• at 480 V</li> <li>• at 600 V</li> </ul> | 5 kA<br>5 kA<br>5 kA             |
| certificate of suitability                                                                           | UL 60947-4-1                     |

#### Further information

Industrial Controls - Product Overview (Catalogs, Brochures,...)

[www.usa.siemens.com/iccatalog](http://www.usa.siemens.com/iccatalog)

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=3RE4121-5AA15-4TB0>

Search Datasheet in Service&Support (Manuals)


<https://support.industry.siemens.com/cs/US/en/ps/3RE4121-5AA15-4TB0/man>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3RE4121-5AA15-4TB0&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RE4121-5AA15-4TB0&lang=en)

Certificates/approvals

<https://support.industry.siemens.com/cs/US/en/ps/3RE4121-5AA15-4TB0/certificate>



| LETTER | KNOCKOUT & CONDUIT SIZE             |
|--------|-------------------------------------|
| A      | ø22.2 FOR 12.7 CONDUIT              |
| B      | ø22.2 X ø28.6 FOR 12.7 & 19 CONDUIT |
| C      | ø28.6 X ø34.9 FOR 19 & 25.4 CONDUIT |

last modified:

1/25/2022