







△ PCB Layout

Dimension

A	$(N-1) \times 10.16 + 6.08$
B	$(N-1) \times 10.16$

N=Number of poles

	TOL	
	2p-6p	7p-12p
A	±0.15	±0.30
B	±0.15	±0.30

SIGN	DATE	DESCRIPTION	APPROVER
△	11/19'07	PCB Layout changed	Tony
△	05/30'11	Wire strip length is changed from 6-7mm to 5-6mm	Steven
△	05/30'11	Add "cULus" Safety Approval logo	Steven

Material:

- Item① Terminal side housing: Thermoplastic (UL94V-0)
- Item② Terminal housing: Thermoplastic (UL94V-0)
- Item③ Terminal cover: Thermoplastic (UL94V-0)
- Item④ Spring clamp: Stainless steel
- Item⑤ Contact pin of short: Brass, Tin plated
- Item⑥ Contact pin of middle: Brass, Tin plated
- Item⑦ Contact pin of long: Brass, Tin plated
- Item⑧ Empty body : Thermoplastic (UL94V-0)

Electrical: cULus

- Voltage rating: 300V
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 12-28
- Stranded wire(AWG): 12-28
- Wire strip length: 5-6mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: cULus
- Critical dimension: ▽

HR xx 4 0 x 1 xxxx G

No. OF POLES

03: 3x1 POLES

06: 3x2 POLES

33: 3x11 POLES

36: 3x12 POLES

COLOR

0: BLACK

5: GREEN (RAL 6018/T)

6: BLUE

8: GREY (RAL 7004/P)

G: Pb<40000ppm

0000: "@" Logo (Standard)

000A: "ANYTEK" Mark

Any special item by customer request. please contact sales department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		HR 10.16mm Series (Solder pins staggered by half the pin spacing)			
PART NO.	HRxx40x1xxxxG			DWG NO.	8HR0103
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Steven 2011.05.30	Tony 2007.11.19		Tolerance
					X. ±0.50
					X.X ±0.30
				UNIT: mm	X.XX ±0.10
				SCALE: NONE	X° ±1°
				SHEET: 01/01	REV.: D