



Sensitivity, $\pm 5\%$, 25°C	500 mV/g
Acceleration range, VDC > 22 V	10 g peak
Amplitude nonlinearity	1%
Frequency response¹:	$\pm 5\%$ 0.7 - 5,000 Hz
	$\pm 10\%$ 0.5 - 9,000 Hz
	± 3 dB 0.2 - 14,000 Hz
Resonance frequency	30 kHz
Transverse sensitivity, max	5% of axial
Temperature response:	-50°C -5%
	+120°C +5%
Power requirement:	
Voltage source	18 - 30 VDC
Current regulating diode	2 - 10 mA
Electrical noise, equiv. g¹:	
Broadband 2.5 Hz to 25 kHz	250 μ g
Spectral 10 Hz	2.5 μ g/ $\sqrt{\text{Hz}}$
	100 Hz 1.5 μ g/ $\sqrt{\text{Hz}}$
	1,000 Hz 1.5 μ g/ $\sqrt{\text{Hz}}$
Output impedance, max	100 Ω
Bias output voltage	12 VDC
Grounding	case isolated, internally shielded
Temperature range	-50° to +120°C
Vibration limit	500 g peak
Shock limit	5,000 g peak
Electromagnetic sensitivity, equiv. g, max	70 μ g/gauss
Sealing	hermetic
Base strain sensitivity, max	0.0002 g/ μ strain
Sensing element design	PZT, shear
Weight	90 grams
Case material	316L stainless steel
Mounting	1/4-28 UNF tapped hole
Mating connector	M12 style, 4 or 5 pin
Recommended cabling	J10 / J9T2A

- High sensitivity
- Certified versions available for use in hazardous areas
- Manufactured in ISO 9001 facility



CE

99117 Rev.B.4 10/19