







P.C.B Layout

Poles	02	03	04	05	06	07	08	09	10	11	12	13
Dim L	10.00	15.00	20.00	25.00	30.00	35.00	40.00	45.00	50.00	55.00	60.00	65.00
Dim B	5.00	10.00	15.00	20.00	25.00	30.00	35.00	40.00	45.00	50.00	55.00	60.00
TOL	±0.15					±0.20					±0.25	
Poles	14	15	16	17	18	19	20	21	22	23	24	
Dim L	70.00	75.00	80.00	85.00	90.00	95.00	100.0	105.0	110.0	115.0	120.0	
Dim B	65.00	70.00	75.00	80.00	85.00	90.00	95.00	100.0	105.0	110.0	115.0	
TOL	±0.25					±0.30						

SIGN	DATE	DESCRIPTION	APPROVER
△	05/20.08	螺絲孔和螺絲進行設置變更	Aaron
△	05/20.08	增加cULus	Aaron
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Item① Terminal cover :Thermoplastic (UL94V-0)
- Item② Terminal housing : Thermoplastic (UL94V-0)
- Item③ Terminal screw : Steel Zinc plating "- " slot type
- Item④ Wire guard solder pin : Brass, Tin plated
- Item⑤ Clamp : Steel stamping, Zinc plating

Electrical cULus

- Voltage rating: 300VAC
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 12-22
- Stranded wire(AWG): 12-22
- Torque(Lb-In): 3.5
- Screw: M2.5
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: 

PART NO.

EQ xx 05 x 0 xxxx G

Poles
02 2Contacts
03 3Contacts
.....
24 24Contacts

Color
0 Black
5 Green
(RAL 6018/T)
6 Blue
8 Grey
(RAL 7035/D)

RoHS
Pb<40,000ppm
0000 Standard @ Logo
000A Standard ANY Logo
Any special item by
customer request,
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		EQ 5.0 Series 90 D Wire inlet (Vertical)							
PART NO.		EQxx05x0xxxxG			DWG NO.		8EQ0003		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.				Tolerance	
		Aaron 2008.05.20	Aaron 2008.05.20					UNIT: mm	
					SCALE: NONE		X.X	±0.30	
					SHEET: 01/01		X.XX	±0.10	
					REV.: C		X*	±1*	