

A1	GND	B12	GND
A2	SSTXP1	B11	SSRXP1
A3	SSTXN1	B10	SSRXN1
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10	SSRXN2	B3	SSTXN2
A11	SSRXP2	B2	SSTXP2
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

NOTE:

1.MATERIAL SPECIFICATION:

- 1.HOUSING: PA9T,UL94 V-0.
- 2.CONTACTS: COPPER ALLOY
- 3.MID PLATE: STAINLESS STEEL

2.PLATING SPECIFICATION:

2-1.CONTACTS:

- Ni 40u" MIN. UNDER PLATED OVER ALL.
- Au PLATED ON THE FUNCTIONAL AREA OF CONTACT.
- (GOLD PLATING THICKNESS FOLLOW THE P/N)
- GOLD FLASH PLATING ON SOLDER AREA

2-2.FRONT SHELL:

- Ni 40u" MIN. UNDER PLATED OVER ALL.

3.MECHANICAL PERFORMANCE:

- 3-1.INSERTION FORCE: 5~20N.
- 3-2.REMOVAL FORCE: 8~20N.
- 3-3.DURABILITY: 10000 CYCLES.

4.ELECTRICAL PERFORMANCE:

- 4-1. CURRENT RATING: 5A
- VOLTAGE RATING: 20V

- 4-2.INSULATION RESISTANCE: 100MΩ MIN



- 4-3.DIELECTRIC WITHSTAND VOLTAGE,AC 100V FOR 1 MINUTE.

5. ENVIRONMENTAL PERFORMANCE:


- OPERATING TEMPERATURE: -30°C~+85°C.

6.IR REFLOW:

- THE PEAK TEMPERATURE ON THE BOARD SHALL BE MAINTAINED FOR 10 SECONDS AT 250°C.



PART NO	L
TYPE-C-31-M-46	1.6
TYPE-C-31-M-46A	1.2
TYPE-C-31-M-46B	0.9
TYPE-C-31-M-46C	0.6



RECOMMEND P.C.B LAYOUT (COMPONENT SIDE)

TOLERANCE FOR PCB LAYOUT IS ± 0.05

APPROVALS		DATE		
DRAWN	LIUCAN	2023.11.6		
CHECKED			TITLE:	USB CONNECTOR
APPROVALS			PART NO.	
TOLERANCES ARE		30~以上	±0.30	ANGLE
		10~30	±0.25	
		5~10	±0.20	UNIT: mm
		~ 5	±0.15	
		±2'	SCALE: 1:1	PROJ: 
			DRAWING NO.	
			SHEET	1 OF 1

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			