


1. ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS
2. TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADER IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD
3. THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
4. HOUSING: FLAME RETARDANT THERMOPLASTIC; COLOR: BLACK.
5. FINISH: 0.000381 [.000015] GOLD ON CONTACT AREA,
ALL OVER 0.00127 [.000050] NICKEL ENTIRE POST.



RECOMMENDED HOLE LAYOUT

99.06	39	40	4-146482-0
[3.984]	[3.900]		
98.65	38	39	3-146482-9
[3.884]	[3.800]		
96.11	37	38	3-146482-8
[3.784]	[3.700]		
93.57	36	37	3-146482-7
[3.684]	[3.600]		
91.03	35	36	3-146482-6
[3.584]	[3.500]		
88.49	34	35	3-146482-5
[3.484]	[3.400]		
85.95	33	34	3-146482-4
[3.384]	[3.300]		
83.41	32	33	3-146482-3
[3.284]	[3.200]		
80.87	31	32	3-146482-2
[3.184]	[3.100]		
78.33	30	31	3-146482-1
[3.084]	[3.000]		
75.79	29	30	3-146482-0
[2.984]	[2.900]		
73.25	28	29	2-146482-9
[2.884]	[2.800]		
70.71	27	28	2-146482-8
[2.784]	[2.700]		
68.17	26	27	2-146482-7
[2.684]	[2.600]		
65.63	25	26	2-146482-6
[2.584]	[2.500]		
63.09	24	25	2-146482-5
[2.484]	[2.400]		
60.55	23	24	2-146482-4
[2.384]	[2.300]		
58.01	22	23	2-146482-3
[2.284]	[2.200]		
55.47	21	22	2-146482-2
[2.184]	[2.100]		
52.93	20	21	2-146482-1
[2.084]	[2.000]		
50.39	19	20	2-146482-0
[1.984]	[1.900]		
47.85	18	19	1-146482-9
[1.884]	[1.800]		
45.31	17	18	1-146482-8
[1.784]	[1.700]		
42.77	16	17	1-146482-7
[1.684]	[1.600]		
40.23	15	16	1-146482-6
[1.584]	[1.500]		
37.69	14	15	1-146482-5
[1.484]	[1.400]		
35.15	13	14	1-146482-4
[1.384]	[1.300]		
32.61	12	13	1-146482-3
[1.284]	[1.200]		
30.07	11	12	1-146482-2
[1.184]	[1.100]		
27.53	10	11	1-146482-1
[1.084]	[1.000]		
24.99	9	10	1-146482-0
[.984]	[.900]		
22.45	8	9	146482-9
[.884]	[.800]		
19.91	7	8	146482-8
[.784]	[.700]		
17.37	6	7	146482-7
[.684]	[.600]		
14.83	5	6	146482-6
[.584]	[.500]		
12.29	4	5	146482-5
[.484]	[.400]		
9.75	3	4	146482-4
[.384]	[.300]		
7.21	2	3	146482-3
[.284]	[.200]		
4.67	1	2	146482-2
[.184]	[.100]		
2.13	-	1	146482-1
[.084]	-		
G	F	E	NO. OF POSITIONS
			PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. 14-MAR-97 CHK. BRANDBERG G. DUBNICZKI APP'D. CUBI 14-MAR-97		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0 P L C ± 1 P L C ± 2 P L C ± 0.51 [0.02] 3 P L C ± 0.10 [0.003] 4 P L C ± 0.012 [0.0005] ANGLES ± =		PRODUCT SPEC APPLICATION SPEC	
MATERIAL		WEIGHT		SIZE CAGE CODE DRAWING NO A1 00779 C 146482	
FINISH		CUSTOMER DRAWING		RESTRICTED TO SCALE 4:1 SHEET 1 OF 1 REV P	