




LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			K	REVISED PER ECO-14-000066	28JUN2014	NK	MM



RECOMMENDED HOLE LAYOUT

OBSOLETE	9	7	1,2,39,40	1,2,39,40	3.984	3.900	39	80	7-104436-0
	8	7	1,2,29,30	1,2,29,30	2.984	2.900	29	60	6-104436-9
	8	7	1,2,24,25	1,2,24,25	2.484	2.400	24	50	6-104436-8
	8	7	1,2,19,20	1,2,19,20	1.984	1.900	19	40	6-104436-7
	8	7	1,2,16,17	1,2,16,17	1.684	1.600	16	34	6-104436-6
	8	7	1,2,14,15	1,2,14,15	1.484	1.400	14	30	6-104436-5
	8	7	1,2,13,14	1,2,13,14	1.384	1.300	13	28	6-104436-4
	8	7	1,2,12,13	1,2,12,13	1.284	1.200	12	26	6-104436-3
	8	7	1,2,11,12	1,2,11,12	1.184	1.100	11	24	6-104436-2
OBSOLETE	9	7	1,2,10,11	1,2,10,11	1.084	1.000	10	22	6-104436-1
	8	7	1,2,9,10	1,2,9,10	.984	.900	9	20	6-104436-0
	8	7	1,2,8,9	1,2,8,9	.884	.800	8	18	5-104436-9
	8	7	1,2,7,8	1,2,7,8	.784	.700	7	16	5-104436-8
OBSOLETE	8	7	1,2,6,7	1,2,6,7	.684	.600	6	14	5-104436-7
	8	7	1,2,5,6	1,2,5,6	.584	.500	5	12	5-104436-6
	8	7	1,2,4,5	1,2,4,5	.484	.400	4	10	5-104436-5
9	OBSOLETE	7	1,2,3,4	1,2,3,4	.384	.300	3	8	5-104436-4
OBSOLETE	8	7	1,2,3	1,2,3	.284	.200	2	6	5-104436-3
	8	7	1,2	1,2	.184	.100	1	4	5-104436-2
		6	1,2,35,36	1,2,35,36	3.584	3.500	35	72	3 2-104436-3
		6	1,2,26,27	1,2,26,27	2.684	2.600	26	54	2 2-104436-2
		6	1,2,21,22	1,2,21,22	2.184	2.100	21	44	3 2-104436-1
		6	1,2,39,40	1,2,39,40	3.984	3.900	39	80	2-104436-0
		6	1,2,29,30	1,2,29,30	2.984	2.900	29	60	1-104436-9
		6	1,2,24,25	1,2,24,25	2.484	2.400	24	50	1-104436-8
		6	1,2,19,20	1,2,19,20	1.984	1.900	19	40	1-104436-7
		6	1,2,16,17	1,2,16,17	1.684	1.600	16	34	1-104436-6
OBSOLETE		6	1,2,14,15	1,2,14,15	1.484	1.400	14	30	1-104436-5
		6	1,2,13,14	1,2,13,14	1.384	1.300	13	28	1-104436-4
		6	1,2,12,13	1,2,12,13	1.284	1.200	12	26	1-104436-3
		6	1,2,11,12	1,2,11,12	1.184	1.100	11	24	1-104436-2
		6	1,2,10,11	1,2,10,11	1.084	1.000	10	22	1-104436-1
		6	1,2,9,10	1,2,9,10	.984	.900	9	20	1-104436-0
		6	1,2,8,9	1,2,8,9	.884	.800	8	18	104436-9
9	SUPERSEDED	6	1,2,7,8	1,2,7,8	.784	.700	7	16	104436-8
	OBSOLETE	6	1,2,6,7	1,2,6,7	.684	.600	6	14	104436-7
		6	1,2,5,6	1,2,5,6	.584	.500	5	12	104436-6
9	SUPERSEDED	6	1,2,4,5	1,2,4,5	.484	.400	4	10	104436-5
		6	1,2,3,4	1,2,3,4	.384	.300	3	8	104436-4
	OBSOLETE	6	1,2,3	1,2,3	.284	.200	2	6	104436-3

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN 6-27-88 H MOLL OK R FEIDT 6-28-88		 TE Connectivity	
DIMENSIONS: INCHES 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLG ± 1 PLG ± 2 PLG ± 3 PLG ±.005 4 PLG ± ANGLES ±		NAME HEADER ASSEMBLY, MOD II, BREAKAWAY, RIGHT ANGLE, DOUBLE ROW, .100X.100 C/L .025 SQ POSITS WITH HOLD-DOWN CONFIGURATIONS	
MATERIAL HOUSING: FLAME RETARDANT THERMO PLASTIC, COLOR: BLACK POSITS: COPPER ALLOY		FINISH SEE TABLE		SIZE CAGE CODE DRAWING NO RESTRICTED TO A1 00779 C=104436	
WEIGHT —		CUSTOMER DRAWING		SCALE 4:1 SHEET 1 OF 1 REV K	