








SEC. A-A

SEC. B-B



SEC. C-C

PART NO. AND CH. CODE	W1	H1	W2	H2	APPLICABLE WIRE SIZE
7114-5276-02	1.25	1.40	1.70	1.74	AWG 28 CABLE DIAMETER 0.85~0.95
7114-7333-02	1.82	2.19	2.45	2.68	ISO 0.35 mm ² ~0.50 mm ² CABLE DIAMETER 1.10~1.70
7114-4618-02	1.85	2.19	2.94	3.13	AWG 22~20 CABLE DIAMETER 1.50~1.90
7114-4619-02	1.96	2.52	2.94	3.13	ISO 0.75 mm ² CABLE DIAMETER 1.50-1.90

					CUSTOMER				MATL. SPEC.				BRASS (t=0.2)		TREAT. & FIN.		COPPER BASE/ TIN PLATING	
					CUSTOMER PART NO.				CUSTOMER DWG NO.				NAME KAIZEN 0.64 TERMINAL MALE					
①	06-24-2011	ADD PART NUMBER		C11-A563	E. Z.													
	07-09-2004	NEW		C04-Z687	Y. I.	OFFICE				TRIAL PART NO.								
LET	DATE	REVISION RECORD		NO.	CHKD	VENDOR												
GENERAL TOLERANCE						VENDOR NO.												
	10MAX	50MAX	100MAX	250MAX	2500VR	ANGLE	ECCENT	DWG TYPE	DWG SOURCE		DWG DATE	UNIT	SCL	ANGLE	PART NO. 7114-4618-02 ETC.			
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30°	0.1	R	NEW		07-09-2004	mm	5/1	3	CH. CODE			
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30°	0.1	APPROVED	CHECKED	CHECKED	DESIGN	DRAWN		DWG NO. 7114-4618-02:R		SET DWG NO.		
③	±0.3	±0.5	±0.8	±1.4	±2	±30°	0.15				Y. ITO	E. ZWART		YAZAKI CORPORATION				
SPECIFIED						MASS g					06-14-2004	06-24-2011						