




LOC 	DIST -	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			W3	REVIDES PER ECR-17-004272	29MAR17	ST	TD



SCALE 2:1



SCALE 3:1

- 1
- BLOCCETTO ADATTO PER TERMINALI FEMMINA PER LA SERIE 6.3 mm FASTON CON RANGO FILO DA 0.8-2.5 MM2. (SUITABLE FOR RECEPTACLE TERMINALS WITH WIRE RANGE 0.8-2.5 mm2).
- 2
- BAVA ACCETTABILE: 0.3 MAX (FLASH PERMISSIBLE: 0.3 MAX.)
- 3
- SPECIFICA DI PRODOTTO: 108-20035 (PRODUCT SPEC.: 108-20035)
- 4
- NON ANCORA RILASCIATO IN PRODUZIONE (NOT YET RELEASED FOR PRODUCTION)

1,2,3	NATURALE (NATURAL)	PA 6 UNFILLED, UL 94-V2 IEC 60335-1, GW 750°C NO FLAME	280232-8	W
1,2,3	NATURALE (NATURAL)	PA 6.6 UL 94-V0 (PA 6.6 UL 94-V0 UNFILLED)	280232-6	U
1,2,3	NERO (BLACK)	PA 6.6 (PA 6.6 UNFILLED)	280232-5	U
1,2,3	ROSSO (RED)		280232-1	U
1,2,3	NATURALE (NATURAL)		280232	U
NOTE	COLORE (COLOUR)	MATERIALE (MATERIAL)	PART NUMBER	REV

		DWN H. YAALI	29OCT2004	TE Connectivity	
		CHK G. TURCO	-		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC ±		POST INSULATION FOR FASTON 6.3 mm series RECEPTACLE CONTACT	
		1 PLC ±0.3			
2 PLC ±		PRODUCT SPEC			
3 PLC ±		SEE NOTE 3			
4 PLC ±		APPLICATION SPEC		SIZE	
ANGLES ±2°		-		CAGE CODE	
FINISH		WEIGHT		DRAWING NO	
MATERIAL SEE TABLE		-		A3 00779C=280232	
		CUSTOMER DRAWING		RESTRICTED TO	
		SCALE 3:1		SHEET 1 OF 1	
				REV W3	