



PCB Layout(Bottom View)

N = Number of poles
Dim A=Nx8.25+2.0
Dim B=(N-1)x8.25

Poles	Tol.	Dim A & B
2-5p		±0.20
6-10p		±0.25
11-16p		±0.35
17-24p		±0.40
25-30p		±0.50

SIGN	DATE	DESCRIPTION	APPROVER
△	8/23'08	Temperature rang changed from -40 ~ 105°C to -40 ~ 115°C	Kind
△	03/17'09	Add stipulation	Seamus
△	06/22'09	The dimension changed from 5.0 to 4.5	Aaron
△	06/04`11	Critical dimension is changed.	Tason
△	06/04`11	The Wire Range is changed from 20-12AWG to 22-12AWG	Tason
△	06/04`11	The tolerance table is changed.	Tason
△	11/27'12	Change the screw plating specification	Jacky
△	12/07'13	Change the withstand voltage and current	Jacky

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

MATERIALS ELECTRICAL	cULus / CQC △
△ RATED VOLTAGE & CURRENT:	300 V, 20 A/300 V, 32 A
△ WITHSTAND VOLTAGE:	AC 2500 V/Min
INSULATION RESISTANCE:	1000 MΩ OR MORE AT DC 500 V
△ OPERATING TEMPERATURE RANG:	-40 °C ~ +115 °C
SCREW TORQUE VALUE:	8.8 Lb-In
WIRE RANGE:	22 - 12 AWG △
1) MOLDED PARTS:	POLYIMIDE 66, UL 94 V-0 BLACK
2) TERMINAL:	BRASS, 0.8t, Tin PLATED
△ 3) TERMINAL SCREWS:	STEEL, M3
△ Critical dimension:	
APPROVAL:	cULus cec △

YK 332 xx 0 x x 00G

NO. OF POLES
02: 2 POLES
03: 3 POLES
04: 4 POLES
:
30: 30 POLES

TERMINAL & SCREW PLATED

- 0: TERMINAL & SCREW: G/F
- 1: TERMINAL: G/F, SCREW: Zinc
- 2: TERMINAL: Sn, SCREW: G/F
- 3: TERMINAL: Sn, SCREW: Zinc

RoHS compliant
(lead<4%) In copper Alloy
MARK
0: "@" MARK
1: "ANY" MARK

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		YK-332 W/O Flange Series						
PART NO.	YK332xx0xx00G			DWG NO.	8YK0001-332			
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance	
		Jacky 2013.12.07	Jacky 2013.12.07				UNIT: mm	X. ±0.50
					SCALE: NONE		X.X ±0.30	
							X.XX ±0.10	
				SHEET: 01/01	REV.: I		X° ±1°	