

INTERCONNECTS

SERIES 316 • 2,54 GRID ELEVATED • SINGLE ROW STRIPS




FIG. 1




FIG. 2




FIG. 3




FIG. 4




FIG. 5

- Elevated socket strips are available in 5 different heights:

316...006 uses pin # 0153-1

316...003 uses pin # 0153-2

316...007 uses pin # 0153-3


316...008 uses pin # 0153-4

316...001 uses pin # 0153-5

See page 167 for details

- Hi-Rel, 4-finger BeCu #30 contact is rated at 3 amps. See page 253 for details

- Insulators are high temperature thermoplastic, suitable for all soldering operations



ORDERING INFORMATION

FIG. 1	Series 316...006	Standoff Height = 5,99		
	316-XX-1-41-006000 Specify number of pins 01-64			
FIG. 2	Series 316...003	Standoff Height = 8,0		
	316-XX-1-41-003000 Specify number of pins 01-64			
FIG. 3	Series 316...007	Standoff Height = 10,21		
	316-XX-1-41-007000 Specify number of pins 01-64			
FIG. 4	Series 316...008	Standoff Height = 11,99		
	316-XX-1-41-008000 Specify number of pins 01-64			
FIG. 5	Series 316...001	Standoff Height = 15,09		
	316-XX-1-41-001000 Specify number of pins 01-64			
RoHS-2 2011/65/EU XX=Plating Code See Below For Electrical, Mechanical & Enviromental Data, See page 264				
SPECIFY PLATING CODE XX=				
Sleeve (Pin)	91	93	41	43
Contact (Clip)	0,25µm Au	0,76µm Au	0,25µm Au	0,76µm Au