

CPS175




Consensic

Data Sheet

Rev 1.0
Sep. 2023
DAT-0054

Manifold Absolute Pressure Sensor



CPS175

Manifold Absolute Pressure Sensor



Overview

The CPS175 is a resistive absolute pressure sensor solution with a fully calibrated pressure compensated analog output for low pressure applications, such as MAP (Manifold Absolute Pressure) systems.

The CPS175 solution comprises of an ultra-small resistive MEMS pressure sensor and a conditioning ASIC for accurate pressure measurements in factory calibrated ranges for the MAP applications. An integrated sigma-delta based ADC combined with internal calibration logic provides a high level analog output signal that is proportional to the applied pressure.

Applications

- Manifold Absolute Pressure
- Industrial Equipment
- Air Control Systems
- Vacuum Systems

Benefits

- Low Power Consumption
- External Clock not Required
- High Resistance to Sensing Media

Features

- Factory Calibrated Pressure Sensor
- Supply Voltage: 5.0V $\pm 10\%$
- Operating Temperature Range: -20°C to +85°C

Interfaces

- Analog Output: Typical 10% to 90% of V_{SUPPLY}

Physical Characteristics

- Small Form Factor, 3 x 5 x 1.2mm (w x l x h)
- LGA Package, 8 Lead
- Top Side Sensing Port



FIGURE 1: CPS175 ANALOG OUTPUT CIRCUIT




TABLE1: ORDERING INFORMATION

PART NUMBER	PRESSURE RANGE	OUTPUT	PACKAGE
CPS175	10 to 115kPa	Analog	8-Lead LGA, Metal Lid, PCB Substrate
SALES and CONTACT INFORMATION sales@consensic.com www.consensic.com			
United States Consensic, Inc. 1900 Powell Street, Suite 600 Emeryville California, 94608, USA Ph: +1 510.588.8735	China Wuxi Consensic Electronics Co., Ltd. No.86, Dicui Road, B5 Building, Fourth Floor, Room 401, Wuxi, Jiangsu Province, 214072 Ph: +86 510.85122279 Fax: +86 510.85122259	无锡康森斯克电子科技有限公司 无锡市滨湖区滴翠路 86 号太湖智谷科技园 北门 B5 栋 4 楼 401 室 邮编: 214072 电话: +86 510.85122279 传真: +86 510.85122259	

CPS175

Manifold Absolute Pressure Sensor



CONTENTS

1	OPERATING CHARACTERISTICS	6
1.1	ABSOLUTE RATINGS	6
1.2	OPERATING CONDITIONS	6
1.3	ELECTRICAL PARAMETERS	7
2	OUTPUT MODES	8
2.1	ANALOG OUTPUT	8
3	OPERATION MODE	9
4	OTP ROM	9
5	CALCULATING OUTPUT	9
5.1	PRESSURE OUTPUT	9
5.1.1	Pressure Output Transfer Function	9
6	PACKAGE AND ASSEMBLY	9
6.1	PIN LAYOUT	10
6.2	MECHANICAL DRAWING	11
6.3	SOLDERING CONDITIONS	12
7	DOCUMENT HISTORY	12
8	DISCLAIMER	13

CPS175

Manifold Absolute Pressure Sensor



LIST OF TABLES

TABLE 1:	ORDERING INFORMATION	3
TABLE 2:	CPS175 PIN DESCRIPTION	10
TABLE 3:	MECHANICAL DIMENSIONS	11
TABLE 4:	PACKAGE REFLOW TEMPERATURE	12

LIST OF FIGURES

FIGURE 1:	CPS175 ANALOG OUTPUT CIRCUIT	3
FIGURE 2:	EXAMPLE OF ANALOG OUTPUT VS. PRESSURE	8
FIGURE 3:	CPS175 PACKAGE PIN LAYOUT	10
FIGURE 4:	LGA WITH METAL LID PACKAGE	11

CPS175

Manifold Absolute Pressure Sensor



1 OPERATING CHARACTERISTICS

1.1 ABSOLUTE RATINGS

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS
Over Pressure					1000 (10)	kPa (bar)
Supply Voltage (with respect to GND)	V_{DD}		-0.3		6.0	V
Voltages at Analog I/O – In Pin	V_{INA}		-0.3		$V_{DD} + 0.3$	V
Voltages at Analog I/O – Out Pin	V_{OUTA}		-0.3		$V_{DD} + 0.3$	V
Storage Temperature	T_{STOR}		-50		130	°C

1.2 OPERATING CONDITIONS

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS
OPERATION						
Supply Voltage to GND ¹	V_S		4.75	5.0	5.25	V
Operating Temperature Range			-20		85	°C
PRESSURE RANGE CHARACTERISTICS						
Range			10 (100)	—	115 (1150)	kPa (mbar)
Full Scale Output	V_{FSO}	@ $V_S=5.0V$	—	4.5	—	V
Full Scale Span	V_{FSS}	@ $V_S=5.0V$	—	4.0	—	V
Accuracy		(0 to 85°C)	—	—	±1.5	% V_{FSS}
Sensitivity	V/P		—	40	—	mV/kPa

CPS175

Manifold Absolute Pressure Sensor



1.3 ELECTRICAL PARAMETERS

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS
SUPPLY CURRENT						
Update Mode Current	I_{DD}	Worst Case Settings: 12-bit, 0ms Power Down		1200	1500	μA
ANALOG OUTPUT						
CPS175	Analog_P	10 to 115kPa (100 to 1150mbar)	0.5		4.5	V
Analog OUTPUT						
Resolution	RES			12		Bits
Analog Additional Error (Including Ratiometricity Error)	Eout	-40 to 125°C		0.1	0.5	%
SYSTEM						
Trimmed System Frequency	f_{SYS}	All Timing in this Specification are Subject to this Variation		1.85		MHz
Start-Up-Time Power-On to Data Ready	t_{STA}	Fastest and Slowest Settings	4.25		173	ms
Update Rate (Normal Mode)	T_{RESP_UP}	Fastest and Slowest Settings	0.70		288	ms
Peak-to-Peak Noise @ Output (100 Measurements in 12-bit)	N_{OUT}			5		LSB

CPS175

Manifold Absolute Pressure Sensor




2 OUTPUT MODES

2.1 ANALOG OUTPUT

The CPS175 provides a ratio metric analog output to applied pressure.

FIGURE 2: EXAMPLE OF ANALOG OUTPUT VS. PRESSURE



CPS175

Manifold Absolute Pressure Sensor



3 OPERATION MODE

The CPS175 is factory programmed in Update Mode only. Measurements are taken continuously.

4 OTP ROM

The OTP ROM array contains the sensor calibration coefficients and the configuration bits for the analog front end, output modes, measurement modes, etc.

5 CALCULATING OUTPUT

The pressure output is a linear transfer function between measured pressure and the input voltage.

5.1 PRESSURE OUTPUT

5.1.1 Pressure Output Transfer Function

$$\text{Pressure (kPa)} = (105V_{\text{out}} - 12.5) / 4$$

6 PACKAGE AND ASSEMBLY

The CPS175 is available in a small land grid array (LGA) package with a metal lid. There is a hole on the lid to allow for external pressure to the sensing diaphragm.

6.1 PIN LAYOUT

FIGURE 3: CPS175 PACKAGE PIN LAYOUT




TABLE 2: CPS175 PIN DESCRIPTION

Pin	Name	Type	Function
1	VDD	P	Connect 0.1uF CAP to GND
2	NC	--	--
3	NC	--	--
4	GND	G	Ground
5	VOUT	O	Voltage output
6	NC	--	Factory use only
7	NC	--	Factory use only
8	NC	--	--

6.2 MECHANICAL DRAWING

FIGURE 4: LGA WITH METAL LID PACKAGE




TABLE 3: MECHANICAL DIMENSIONS

DIMENSION	MIN.	TYP.	MAX.	UNITS
Length		5		mm
Width		3		mm
Height		1.265		mm
Pad 1 Length		0.5		mm
Pad 1 Width		1.2		mm
Pad 2 to 8 Length		0.5		mm
Pad 2 to 8 Width		0.8		mm
Pad Pitch(Y-Axis)		2		mm
Pad Pitch(X-Axis)		1.25		mm
Port Hole Diameter		0.5		mm

CPS175

Manifold Absolute Pressure Sensor



6.3 SOLDERING CONDITIONS

TABLE 4: PACKAGE REFLOW TEMPERATURE

PARAMETER	CONDITIONS	MIN	TYP	MAX	UNITS
Soldering Peak Temperature	Less than 30 seconds (JEDEC-STD-020 Standard)			260	°C

7 DOCUMENT HISTORY

REVISION	DATE	DESCRIPTION
1.0	21-Sep-2023	Preliminary Release

8 DISCLAIMER

Information in this datasheet is provided solely to enable implementation and use of Consensic products. The specifications and characteristics are subject to change without notice. Consensic reserves the right to make changes without further notice to any products herein.

“Typical” parameters provided in this datasheet can and do vary in different applications and actual performance may vary over time. Customers must validate all operating parameters for their application.

Consensic is not responsible for direct, indirect, incidental or consequential damages resulting from any defect, error or failure to perform. In no event, regardless of cause, shall Consensic incur any liability for any damages of any kind, including, but not limited to, any direct, indirect, special, incidental, punitive or consequential damages arising out of, resulting from, or any way connected to the use of the product, whether arising under breach of contract, tort (including negligence), strict liability or otherwise, and whether based on this agreement or otherwise, even if advised of the possibility of such damages, and whether or not injury was sustained by persons or property or otherwise; and whether or not loss was sustained from, or arose out of, the results of, the product, or any services that may be provided by Consensic.

The customer assumes all responsibility and liability for proper and safe handling of the goods. It is the customer’s responsibility to take any and all appropriate precautions with regard to electrostatic discharge. Also be aware that the products herein may not be regulatory compliant or agency certified (FCC, UL, CE, etc.).

No License is granted under any patent right or other intellectual property whatsoever. Consensic assumes no liability for applications assistance, customer product design, software performance, or infringement of patents or any other Intellectual property rights of any kind.