

INTERCONNECTS

SERIES 329, 380, 429, 480 • 2,54 GRID SOLDER CUP HEADERS AND SOCKETS • SINGLE AND DOUBLE ROW STRIPS




FIG. 1




FIG. 2




FIG. 3





FIG. 4

- Series 380 & 480 use MM #8000 pins. See page 216 for details
- Series 329 & 429 use MM #2954 receptacles and accept pin diameters from 0,38 - 0,64. See page 171 for details
- Series 329 & 429 receptacles use Hi-Rel, 4-finger BeCu #30 contact rated at 3 amps. See page 253 for details
- Soldercups are pre-aligned
- Insulators are high temperature thermoplastic, suitable for all soldering operations



ORDERING INFORMATION

FIG. 1	Series 380...001 Single Row Solder Cup / Solder Tail	
	380-XX-1	-00-001000
	Specify number of pins	01-64
FIG. 2	Series 480...001 Double Row Solder Cup / Solder Tail	
	480-10-2	-00-001000
	Specify number of pins	02-64
RoHS-2 2011/65/EU XX=Plating Code See Below For Electrical, Mechanical & Environmental Data, See page 264		
SPECIFY PLATING CODE XX=		
Pin Plating	10	90
	0,25µm Au	5,08µm Sn/Pb
		5,08µm Sn

FIG. 3	Series 329...540 Single Row Solder Cup Sockets	
	329-XX-1	-41-540000
	Specify number of pins	01-64
FIG. 4	Series 429...540 Double Row Solder Cup Sockets	
	429-XX-2	-41-540000
	Specify number of pins	02-64
RoHS-2 2011/65/EU XX=Plating Code See Below For Electrical, Mechanical & Environmental Data, See page 264		
SPECIFY PLATING CODE XX=		
Sleeve (Pin)	11	13
	0,25µm Au	0,25µm Au
Contact (Clip)	41	43
	0,25µm Au	0,76µm Au
		5,08µm Sn
		0,25µm Au
		0,76µm Au

