




△
Φ5.4 Depth=6.0



YK 315 xx 3 x x 00 G

NO. OF POLES
02: 2 POLES
03: 3 POLES
04: 4 POLES
:
30: 30 POLES

G:RoHS compliant(lead<4%)
in copper alloy

MARK
0: "@" MARK
1: "ANY" MARK

TERMINAL & SCREW PLATED
0: TERMINAL & SCREW: G/F
△ 1: TERMINAL: G/F, SCREW: Zinc
2: TERMINAL: Sn, SCREW: G/F
△ 3: TERMINAL: Sn, SCREW: Zinc


N= Number of poles △

DIM		TOL				
		2P-5P	6P-10P	11P-16P	17P-24P	25P-30P
Dim A	$(N+2) \times 7.62 + 1.5$	±0.20	±0.25	±0.35	±0.40	±0.50
Dim B	$(N-1) \times 7.62$	±0.20	±0.25	±0.35	±0.40	±0.50

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		YK-315 W/ Flange Series				
PART NO.	YK315xx3xx00G			DWG NO.	8YK0002-315	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.		
		Jacky 2012.11.21	Jacky 2012.11.21		Tolerance	
					UNIT: mm	X. ±0.50
					SCALE: NONE	X.X ±0.30
					REV.: C	X.XX ±0.10
				SHEET: 01/01		X° ±1°