



REV.	ECN NO OR DESCRIPTION	REVISED	DATE

NOTES:
MATERIAL
1.HOUSING MATERIAL: THERMOPLASTIC BLACK UL94V-0.
2.CONTACT MATERIAL: C5191 R-H T=0.3MM
3.SHELL: SUS304 T=0.2MM
FINISH:
1.CONTACT PLATING:GOLD PLATING OVER NICKEL.
ELECTRICAL:
1.VOLTAGE RATING:125 VAC RMS
2.CURRENT RATING:1.5 AMP
3.CONTACT RESISTANCE: 30 MILLIOHMS MAX
4.INSULATION RESISTANCE:500 MEGOHMS MIN @ 500V DC
5.DIELECTRIC WITHSTANDING VOLTAGE :500V AC R.M.S MIN
MECHANICAL:
1.DURRABILITY: 750 CYCLES MIN

LED ELECTRICAL CHARACTERISTIC			
Orange	Green		
9-10	11-12		
LEFT LED	RIGHT LED		

Standard LED	Wavelength	Forward V (Min/Max)	Forward A	Type
Green	568nm	1.8v/2.8v	20mA	squareness
Yellow	585nm	1.8v/2.8v	20mA	squareness
Orange	610nm	1.8v/2.8v	20mA	squareness

UNLESS OTHERWISE SPECIFIED TOLERANCES		东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD			
DECIMALS:	ANGLES:	TITLE	RJ45 沉板式9.9H板上2.95H带灯左橙右绿		
X :±0.35	X :±2°	DWN	xiong	PART NO. RJ45-881A11-3	
X.X :±0.25	X.X :±1°	CHKD	lee	SCALE:1:1	UNIT: mm
X.XX :±0.15		APVD	wang	SIZE: A4	SHEET:10F 1
CUSTOMER COPY					