



Diagram of a 15-pin D-sub connector. Pin 14 is labeled 'LEFT LED' and pin 15 is labeled 'RIGHT LED'.

LED LAYOUT

LED Specification

Standard LED Color	LED Wavelength	Forward(A)	Forward
Yellow	568nm	20mA	1.85-2.4
Green	585nm	20mA	1.7-2.2



			GENERAL TOLERANCE	制 图 DRAWING	 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM TOL	审 核 CHECK				
			X.X ±0.30	批 准 APPROVAL	产品名称 TITLE	网络插座 (2x8 带灯无弹)	版 本 REV.	A
1	初版发行		X.XX ±0.20	比 例 SCALE	产品料号 PART NO.	HC-RJ45-059D-2x8-2-04	单 位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日 期 MODIFY DATE	X.XXX ±0.10	投 影 Projection	材 料 MATERIAL		页 次 SHEET	1/1
			Angle ±3.0°					


 深圳市华灿天禄电子有限公司

ShenzhenhuacantianluELECTRONICS CO., LTD

产品名称
TITLE

网络插座 (2x8 带灯无弹)

版本 REV.	
------------	--

A

产品料号
PART NO.

HC-RJ45-059D-2x8-2-04

单位
UNITS

mm

材料
MATERIAL

--	--

页次
SHEET

1/