



REV.	ECN NO OR DESCRIPTION	REVISED	DATE

NOTES

MATERIAL

1. HOUSING MATERIAL: PBT/PA46 BLACK UL94V-0.
2. CONTACT MATERIAL: PHOSPHOR BRONZE $\phi 0.46\text{mm}$.
3. PLATING: GOLD FLASH PLATING OVER NICKEL.

ELECTRICAL


1. VOLTAGE RATING: 125 VAC RMS.
2. CURRENT RATING: 1.5 AMP.
3. CONTACT RESISTANCE: 40 MILLIOHMS MAX.
4. INSULATION RESISTANCE: 500 MEGOHMS MIN @ 100V DC .
5. DIELECTRIC DIELECTRIC RESISTANCE: 500V DC RMS 50Hz. 1MIN.

MECHANICAL

1. DURRABILITY: 750 CYCLES MIN.
2. MATING/UNMATING FORC: 2.24 KG. F MAX.

ENVIRONMENTAL:

1. OPERATION: $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$.
2. STORAGE: $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$.



RJ45-401-05-23

流水码

21: PBT黑 盘装

23: PA46黑 盘装

类别码

05: 有壳无灯F3.05

UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS: ANGLES:
X :±0.35 X :±2°
X.X :±0.25 X.X :±1°
X.XX :±0.15



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE	RJ45 5244立式有壳无灯F3.05 DIP PA46黑			
DWN	xiong	PART NO. RJ45-401-05-23		
CHKD	lee	SCALE: 1:1	UNIT: mm	
APVD	wang	SIZE: A4	SHEET: 10F 1	REV: A4

CUSTOMER COPY