





REV.	ECN NO OR DESCRIPTION	REVISED	DATE



8	—
7	—
6	RX-
5	—
4	—
3	RX+
2	TX-
1	TX+
PIN序说明	

NOTES

MATERIAL

1. HOUSING MATERIAL: GLASS FILLED POLYESTER UL94V-0.
2. CONTACT MATERIAL: PHOSPHOR BRONZE $\phi 0.46\text{mm}$.
3. PLATING: GOLD PLATING OVER NICKEL.
4. SHIELD: SUS 201 T=0.20mm WITH NICKEL PLATED.

ELECTRICAL



1. VOLTAGE RATING: 125 VAC RMS.
2. CURRENT RATING: 1.5 AMP.
3. CONTACT RESISTANCE: 30 MILLIOHMS MAX.
4. INSULATION RESISTANCE: 500 MEGOHMS MIN @ 500V DC .
5. DIELECTRIC DIELECTRIC RESISTANCE: 500V AC RMS 50Hz. 1MIN.

MECHANICAL


1. DURRABILITY: 750 CYCLES MIN.

ENVIRONMENTAL:

1. STORAGE: $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$.
2. OPERATION: $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$.



PCB LAYOUT



UNLESS OTHERWISE SPECIFIED TOLERANCES		东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD			
DECIMALS:		TITLE			
X	:±0.30	5621 1x1有壳F3.05 DIP-0.5u淡PA46黑			
X.X	:±0.20	DWN	xiong	PART NO. RJ3306-005-B	
X.XX	:±0.10	CHKD	lee	SCALE:1:1	UNIT: mm
		APVD	wang	SIZE: A4	SHEET:10F 1
		CUSTOMER COPY			
		REV: A4			