





SIGN	DATE	DESCRIPTION	APPROVER
△	7/17'08	The dimension changed from 4.5 to 4.9	kind
△	7/17'08	Temp.range changed from -40℃~105℃ to -40℃~115℃	kind
△	11/20'12	Change the screw plating specification	Jacky
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			



MATERIALS ELECTRICAL
RATED VOLTAGE & CURRENT: 300 V, 15 A
WITHSTAND VOLTAGE: AC 2000 V/Min
INSULATION RESISTANCE: 1000 MΩ OR MORE AT DC 500 V
△ OPERATING TEMPERATURE RANGE: -40 °C ~+115 °C
SCREW TORQUE VALUE: 5.2 Lb-In.
WIRE RANGE: 14 ~ 22 AWG
1) MOLDED PARTS: THERMOPLASTIC, UL 94 V-0 BLACK
2) TERMINAL: BRASS, 0.8t, Tin PLATED
△ 3) TERMINAL SCREWS: STEEL, M3
Critical dimension: ▽

PART No.: YK 303xx 0 x x 00G
NO. OF POLES
02: 2 POLES
03: 3 POLES
04: 4 POLES
:
20: 20 POLES
G:RoHS compliant(lead<4%)
in copper alloy
MARK
0: "0" MAK
1: "ANY" MAK
TERMINAL & SCREW PLATED
0: TERMINAL & SCREW: G/F
△ 1: TERMINAL: G/F, SCREW: Zinc
2: TERMINAL: Sn, SCREW: G/F
△ 3: TERMINAL: Sn, SCREW: Zinc

DIM		TOL			
		2P-4P	5P-10P	11P-16P	17P-20P
Dim A	(N-1)×7.62+9.54	±0.20	±0.30	±0.40	±0.50
Dim B	(N-1)×7.62	±0.20	±0.30	±0.40	±0.50



P.C.B LAYOUT(Top View)

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	YK-303 W/o Flange & W/o cover Series							
PART NO.	YK303xx0xx00G			DWG NO.	8YK0001-303			
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance	
		Jacky 2012.11.20	Jacky 2012.11.20			UNIT: mm	X. ±0.50	
						SCALE: NONE	X.X ±0.30	
				SHEET: 01/01		REV.: D	X.XX ±0.10	
							X° ±1°	