



REV.	ECN NO OR DESCRIPTION	REVISED	DATE

NOTES

MATERIAL

1. HOUSING MATERIAL: GLASS FILLED POLYESTER UL94V-0.
2. CONTACT MATERIAL: PHOSPHOR BRONZE $\phi 0.46\text{mm}$.
3. PLATING: GOLD FLASH PLATING OVER NICKEL.
4. SHIELD: BRASS T=0.2mm NICKEL PLATING.

ELECTRICAL

1. VOLTAGE RATING: 125 VAC RMS.
2. CURRENT RATING: 1.5 AMP.
3. CONTACT RESISTANCE: 40 MILLIOHMS MAX.
4. INSULATION RESISTANCE: 500 MEGOHMS MIN @ 100V DC .
5. DIELECTRIC DIELECTRIC RESISTANCE: 500V DC RMS 50Hz. 1MIN.




MECHANICAL

1. DURRABILITY: 750 CYCLES MIN.
2. MATING/UNMATING FORC:2.24 KG.F MAX.


ENVIRONMENTAL:

1. STORAGE: $-40^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
2. OPERATION: $-40^{\circ}\text{C}\sim+85^{\circ}\text{C}$.

8	—
7	—
6	RX-
5	—
4	—
3	RX+
2	TX-
1	TX+
PIN序	说明



PC Board Layout



UNLESS OTHERWISE SPECIFIED TOLERANCES		东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD			
DECIMALS:	ANGLES:	TITLE	5921 1x1无弹左黄右绿B3.05 DIP GF PA46黑		
X :±0.30	X :±2°	DWN	xiong	PART NO.	RJ3303-010-32
X.X :±0.20	X.X :±1°	CHKD	lee	SCALE:1:1	UNIT: mm
X.XX :±0.10		APVD	wang	SIZE: A4	SHEET:10F 1
CUSTOMER COPY					