


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		N	REVISED PER ECO-19-002381	06MAR2019	AP	DG

ACCESSORIES	5	BUSHING WITH THROUGH-HOLE 3,1 DIA.					2					2						
	5	BUSHING WITH INNER THREAD 4-40 UNC						2					2					
	5	BUSHING WITH INNER THREAD M3							2					2				
	4	FEMALE SCREWLOCK WITH 4-40 UNC								2						2		
	4	FEMALE SCREWLOCK WITH M3									2						2	
	7	BOARDLOCK					2	2	2	2	2							
	ITEM NO.	DESCRIPTION OF ACCESSORY																
	106507-2																	
	1-106507-2																	
	2-106507-2																	
	3-106507-2																	
	4-106507-2																	
	5-106507-2																	
	6-106507-2																	
	7-106507-2																	
	8-106507-2																	
	9-106507-2																	



- 1 GROOVE INDICATES VERSION WITH 4-40 UNC INNER THREAD; WITHOUT GROOVE INDICATES VERSION WITH M3 INNER THREAD.
2 CAVITY IDENTIFICATION AT FRONT SIDE ONLY.
3 PART NUMBER AND DATE CODE.

4. AIR AND CREEPAGE DISTANCES ACCORDING TO DIN 41652.
5. CONTACT FINISH: GOLD FLASH OVER PALLADIUM-NICKEL PLATE OR GOLD PLATE ON THE MATING SURFACES, TIN PLATE ON THE SOLDER-TAILS, NICKEL UNDERPLATE ON THE ENTIRE CONTACT. MATING SURFACE MEETS PERFORMANCE LEVEL 2 PER DIN 41652.

- ITEM NO./MATERIAL :
- 1 SHELL : BRIGHT TIN PLATED STEEL
 - 2 HOUSING : GLASS FILLED POLYESTER, COLOR : BLACK
 - 3 CONTACTS : PHOSPHOR BRONZE (PLATING : SEE NOTES ABOVE)
 - 4 FEMALE SCREWLOCK : TIN PLATED STEEL (INNER THREAD 4-40 UNC OR M3)
 - 5 BUSHING : TIN PLATED STEEL (INNER THREAD 4-40 UNC OR M3 OR 3,1 DIA THROUGH-HOLE)
 - 6 BRACKET : TIN PLATED STEEL
 - 7 BOARDLOCK : TIN PLATED PHOSPHOR BRONZE
 - 8 POST ALIGNMENT PLATE : GLASS FILLED NYLON. COLOR : BLACK

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2009		DWN D. KESSLER	14JAN99	TE Connectivity			
		CHK W. SOOMERS	-				
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
		0 PLC	± -	PRODUCT SPEC			
		1 PLC	± 0.3				
		2 PLC	± 0.15	APPLICATION SPEC			
		3 PLC	± -				
		4 PLC	± -	WEIGHT			
		ANGLES	± 2°				
MATERIAL		FINISH		SIZE			
				CAGE CODE			
				DRAWING NO			
				RESTRICTED TO			
				A2 00779 C=106507			
				SCALE			
				NTS			
				SHEET			
				1 OF 1			
				REV			
				N			
				CUSTOMER DRAWING			

D

C

B

A

D

C

B

A

106507