



LOC	DIST	REVISIONS					
FT	0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			G11	REVISED PER ECO-14-000579	10MAY2014	NK	MM



08±0.08
TYP

2.54 REF
2 PLC

WIRE ENTRY



- INK MARKING, WHITE COLOR.

PRELIMINARY	-	0.8μm GOLD	106.68±0.35	21	5-796635-8
PRELIMINARY	-	0.8μm GOLD	86.36±0.30	17	5-796635-7
PRELIMINARY	-	0.8μm GOLD	71.12	14	5-796635-6
PRELIMINARY	-	0.8μm GOLD	60.96	12	5-796635-5
PRELIMINARY	-	0.8μm GOLD	50.80	10	5-796635-4
PRELIMINARY	-	0.8μm GOLD	40.64	8	5-796635-3
PRELIMINARY	-	0.8μm GOLD	35.56	7	5-796635-2
PRELIMINARY	-	0.8μm GOLD	30.48	6	5-796635-1
PRELIMINARY	-	0.8μm GOLD	25.40	5	5-796635-0
PRELIMINARY	-	0.8μm GOLD	20.32±0.15	4	4-796635-9
PRELIMINARY	-	0.8μm GOLD	15.24±0.15	3	4-796635-8
PRELIMINARY	-	0.8μm GOLD	10.16±0.15	2	4-796635-7
	DETAIL R	TIN	45.72	9	4-796635-6
	DETAIL P	TIN	10.16±0.15	2	4-796635-5
	-	0.8μm GOLD	20.32±0.15	4	4-796635-4
	-	0.8μm GOLD	45.72	9	4-796635-3
	DETAIL N	TIN	86.36±0.30	17	4-796635-2
	DETAIL M	TIN	66.04	13	4-796635-1
PRELIMINARY	DETAIL L	TIN	60.96	12	4-796635-0
	DETAIL K	TIN	15.24±0.15	3	3-796635-9
	DETAIL J	TIN	81.28±0.30	16	3-796635-8
	DETAIL H	TIN	15.24±0.15	3	3-796635-7
	-	GOLD	30.48±0.20	6	3-796635-6
	-	TIN	127.00±0.35	25	2-796635-5
	-	TIN	121.92±0.35	24	2-796635-4
	-	TIN	116.84±0.35	23	2-796635-3
	-	TIN	111.76±0.35	22	2-796635-2
	-	TIN	106.68±0.35	21	2-796635-1
	-	TIN	101.60±0.35	20	2-796635-0
	-	TIN	96.52±0.35	19	1-796635-9
	-	TIN	91.44±0.30	18	1-796635-8
	-	TIN	86.36±0.30	17	1-796635-7
	-	TIN	81.28±0.30	16	1-796635-6
	-	TIN	76.20±0.30	15	1-796635-5
	-	TIN	71.12	14	1-796635-4
	-	TIN	66.04	13	1-796635-3
	-	TIN	60.96	12	1-796635-2
	-	TIN	55.88	11	1-796635-1
	-	TIN	50.80	10	1-796635-0
	-	TIN	45.72	9	796635-9
	-	TIN	40.64	8	796635-8
	-	TIN	35.56±0.20	7	796635-7
	-	TIN	30.48±0.20	6	796635-6
	-	TIN	25.40±0.20	5	796635-5
	-	TIN	20.32±0.15	4	796635-4
	-	TIN	15.24±0.15	3	796635-3
	-	TIN	10.16±0.15	2	796635-2
	MARKING	CONTACT FINISH	L	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. WELDON 180CT2000 CHK D. BIEVENOUR 180CT2000 APVD D. BIEVENOUR 180CT2000		 TE Connectivity			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC $\pm$. 1 PLC $\pm$ 0.3 2 PLC $\pm$ 0.25 3 PLC $\pm$ 0.000 4 PLC $\pm$ 0.0000 ANGLES $\pm$ 2°		NAME TERMINAL BLOCK, PLUG, STACKING, 5.08mm PITCH			
		PRODUCT SPEC -		APPLICATION SPEC -			
MATERIAL		FINISH		SIZE A2		GAGE CODE 00779	DRAWING NO C-796635
				WEIGHT -		RESTRICTED TO -	
				CUSTOMER DRAWING			
				SCALE 2:1		SHEET 1 OF 2	
						REV G11	

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

LOC

DIST

FT

0

P

LTR

REVISIONS

DESCRIPTION

DATE

DWN

APVD

-

SEE SHEET 1

-

-

-

A

B

S

DETAIL H

1

2

3

4

5

6

7

8

9

10

11

12

13

14

15

16

DETAIL J

+ - COM

RS485

DETAIL K

1

2

3

4

5

6

7

8

9

10

11

12

DETAIL L

1

2

3

4

5

6

7

8

9

10

11

12

13

DETAIL M

1

2

3

4

5

6

7

8

9

10

11

12

13

14

15

16

17

DETAIL N

1

2

DETAIL P

1

2

3

4

5

6

7

8

9

DETAIL R

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

S. WELDON

18OCT2000

CHK

D. BIEVENOUR

18OCT2000

APVD

D. BIEVENOUR

18OCT2000

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

DIMENSIONS:

mm

0 PLC

±

-

1 PLC

±0.2

2 PLC

±0.0

3 PLC

±0.000

4 PLC

±0.0000

ANGLES

±2°

FINISH

MATERIAL

-

TE

TE Connectivity

NAME

TERMINAL BLOCK, PLUG, STACKING,
5.08mm PITCH

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A200779

C-796635

-

SCALE

2:1

SHEET

2

OF

2

REV

G11

1471-9 (3/11)