

APM2701CGC-TRG-VB Datasheet

N- and P-Channel 20V (D-S) MOSFET

PRODUCT SUMMARY


	V_{DS} (V)	$R_{DS(on)}$ (Ω)	I_D (A)
N-Channel	20	0.022 at $V_{GS} = 10$ V	5.5
		0.030 at $V_{GS} = 4.5$ V	4.2
P-Channel	- 20	0.055 at $V_{GS} = - 10$ V	- 3.4
		0.079 at $V_{GS} = - 4.5$ V	- 2.5

FEATURES

- Halogen-free According to IEC 61249-2-21 Definition
- Trench Power MOSFET
- 100 % R_g Tested
- Compliant to RoHS Directive 2002/95/EC



RoHS
COMPLIANT
HALOGEN
FREE
Available



N-Channel MOSFET



P-Channel MOSFET

ABSOLUTE MAXIMUM RATINGS $T_A = 25^\circ\text{C}$, unless otherwise noted

Parameter		Symbol	N-Channel	P-Channel	Unit
Drain-Source Voltage		V _{DS}	20	- 20	V
Gate-Source Voltage		V _{GS}	± 20	± 20	
Continuous Drain Current (T _J = 150 °C) ^{a, b}	T _A = 25 °C	I _D	5.5	- 3.4	A
	T _A = 70 °C		4.0	- 2.3	
Pulsed Drain Current		I _{DM}	15	10	
Continuous Source Current (Diode Conduction) ^{a, b}		I _S	1.05	- 1.05	
Maximum Power Dissipation ^{a, b}	T _A = 25 °C	P _D	1.15		W
	T _A = 70 °C		0.73		
Operating Junction and Storage Temperature Range		T _J , T _{stg}	- 55 to 150		°C

THERMAL RESISTANCE RATINGS

Parameter	Symbol	Typical	Maximum	Unit
Maximum Junction-to-Ambient ^a	R_{thJA}	93	110	$^\circ\text{C/W}$
		130	150	
Maximum Junction-to-Lead	R_{thJL}	75	90	

Notes:

a. Surface Mounted on FR4 board.

b. $t \leq 5$ s.

SPECIFICATIONS T _J = 25 °C, unless otherwise noted							
Parameter	Symbol	Test Conditions		Min.	Typ.	Max.	Unit
Static							
Gate Threshold Voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _D = 250 μA	N-Ch	0.5	0.8	1.5	V
		V _{DS} = V _{GS} , I _D = - 250 μA	P-Ch	- 0.5	-0.8	-1.5	
Gate-Body Leakage	I _{GSS}	V _{DS} = 0 V, V _{GS} = ± 8 V	N-Ch P-Ch			± 100 ± 100	nA
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} = 16 V, V _{GS} = 0 V	N-Ch			1	μA
		V _{DS} = - 16 V, V _{GS} = 0 V	P-Ch			- 1	
		V _{DS} = 16 V, V _{GS} = 0 V, T _J = 55 °C	N-Ch			5	
		V _{DS} = - 16 V, V _{GS} = 0 V, T _J = 55 °C	P-Ch			- 5	
On-State Drain Current ^a	I _{D(on)}	V _{DS} = 5 V, V _{GS} = 10 V	N-Ch	3.7			A
		V _{DS} = - 5 V, V _{GS} = - 10 V	P-Ch	- 3			
Drain-Source On-State Resistance ^a	R _{DS(on)}	V _{GS} = 10 V, I _D = 2.5 A	N-Ch		0.022		Ω
		V _{GS} = - 10 V, I _D = - 1.8 A	P-Ch		0.055		
		V _{GS} = 4.5 V, I _D = 2.0 A	N-Ch		0.030		
		V _{GS} = - 4.5 V, I _D = - 1.2 A	P-Ch		0.079		
Forward Transconductance ^a	g _{fs}	V _{DS} = 10 V, I _D = 2.5 A	N-Ch		4.3		S
		V _{DS} = - 15 V, I _D = - 1.8 A	P-Ch		2.4		
Diode Forward Voltage ^a	V _{SD}	I _S = 1.05 A, V _{GS} = 0 V	N-Ch		0.81	1.10	V
		I _S = - 1.05 A, V _{GS} = 0 V	P-Ch		- 0.83	- 1.10	
Dynamic ^b							
Total Gate Charge	Q _g	N-Channel V _{DS} = 15 V, V _{GS} = 5 V, I _D = 1.8 A	N-Ch P-Ch		2.1 2.4	3.2 3.6	nC
Gate-Source Charge	Q _{gs}		N-Ch P-Ch		0.7 0.9		
Gate-Drain Charge	Q _{gd}	P-Channel V _{DS} = - 15 V, V _{GS} = - 5 V, I _D = - 1.8 A	N-Ch P-Ch		0.7 0.8		
Gate Resistance	R _g		N-Ch P-Ch	0.5 3		2.4 11	Ω
Turn-On Delay Time	t _{d(on)}	N-Channel V _{DD} = 15 V, R _L = 15 Ω I _D ≅ 1 A, V _{GEN} = 10 V, R _g = 6 Ω	N-Ch P-Ch		7 8	11 12	ns
Rise Time	t _r		N-Ch P-Ch		9 12	14 18	
Turn-Off Delay Time	t _{d(off)}	P-Channel V _{DD} = - 15 V, R _L = 15 Ω	N-Ch P-Ch		13 12	20 18	
Fall Time	t _f	I _D ≅ - 1 A, V _{GEN} = - 10 V, R _g = 6 Ω	N-Ch P-Ch		5 7	8 11	
Source-Drain Reverse Recovery Time	t _{rr}	I _F = 1.05 A, dI/dt = 100 A/μs	N-Ch		35	60	
		I _F = - 1.05 A, dI/dt = 100 A/μs	P-Ch		30	60	

Notes:

a. Pulse test; pulse width $\leq 300\ \mu\text{s}$, duty cycle $\leq 2\%$.

b. Guaranteed by design, not subject to production testing.

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.


N-CHANNEL TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted



Output Characteristics



Transfer Characteristics



On-Resistance vs. Drain Current



Capacitance





Gate Charge




On-Resistance vs. Junction Temperature





N-CHANNEL TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted





N-CHANNEL TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted




P-CHANNEL TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted



P-CHANNEL TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted




P-CHANNEL TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted




TSOP: 5/6-LEAD



JEDEC Part Number: MO-193C



5-LEAD TSOP



6-LEAD TSOP



	MILLIMETERS			INCHES		
Dim	Min	Nom	Max	Min	Nom	Max
A	0.91	-	1.10	0.036	-	0.043
A ₁	0.01	-	0.10	0.0004	-	0.004
A ₂	0.90	-	1.00	0.035	0.038	0.039
b	0.30	0.32	0.45	0.012	0.013	0.018
c	0.10	0.15	0.20	0.004	0.006	0.008
D	2.95	3.05	3.10	0.116	0.120	0.122
E	2.70	2.85	2.98	0.106	0.112	0.117
E ₁	1.55	1.65	1.70	0.061	0.065	0.067
e	0.95 BSC			0.0374 BSC		
e ₁	1.80	1.90	2.00	0.071	0.075	0.079
L	0.32	-	0.50	0.012	-	0.020
L ₁	0.60 Ref			0.024 Ref		
L ₂	0.25 BSC			0.010 BSC		
R	0.10	-	-	0.004	-	-
θ	0°	4°	8°	0°	4°	8°
θ ₁	7° Nom			7° Nom		
ECN: C-06593-Rev. I, 18-Dec-06						
DWG: 5540						

RECOMMENDED MINIMUM PADS FOR TSOP-6



Recommended Minimum Pads
Dimensions in Inches/(mm)

Disclaimer

All products due to improve reliability, function or design or for other reasons, product specifications and data are subject to change without notice.

Taiwan VBsemi Electronics Co., Ltd., branches, agents, employees, and all persons acting on its or their representatives (collectively, the "Taiwan VBsemi"), assumes no responsibility for any errors, inaccuracies or incomplete data contained in the table or any other any disclosure of any information related to the product.(www.VBsemi.com)

Taiwan VBsemi makes no guarantee, representation or warranty on the product for any particular purpose of any goods or continuous production. To the maximum extent permitted by applicable law on Taiwan VBsemi relinquished: (1) any application and all liability arising out of or use of any products; (2) any and all liability, including but not limited to special, consequential damages or incidental ; (3) any and all implied warranties, including a particular purpose, non-infringement and merchantability guarantee.

Statement on certain types of applications are based on knowledge of the product is often used in a typical application of the general product VBsemi Taiwan demand that the Taiwan VBsemi of. Statement on whether the product is suitable for a particular application is non-binding. It is the customer's responsibility to verify specific product features in the products described in the specification is appropriate for use in a particular application. Parameter data sheets and technical specifications can be provided may vary depending on the application and performance over time. All operating parameters, including typical parameters must be made by customer's technical experts validated for each customer application. Product specifications do not expand or modify Taiwan VBsemi purchasing terms and conditions, including but not limited to warranty herein.

Unless expressly stated in writing, Taiwan VBsemi products are not intended for use in medical, life saving, or life sustaining applications or any other application. Wherein VBsemi product failure could lead to personal injury or death, use or sale of products used in Taiwan VBsemi such applications using client did not express their own risk. Contact your authorized Taiwan VBsemi people who are related to product design applications and other terms and conditions in writing.

The information provided in this document and the company's products without a license, express or implied, by estoppel or otherwise, to any intellectual property rights granted to the VBsemi act or document. Product names and trademarks referred to herein are trademarks of their respective representatives will be all.

Material Category Policy

Taiwan VBsemi Electronics Co., Ltd., hereby certify that all of the products are determined to be RoHS compliant and meets the definition of restrictions under Directive of the European Parliament 2011/65 / EU, 2011 Nian. 6. 8 Ri Yue restrict the use of certain hazardous substances in electrical and electronic equipment (EEE) - modification, unless otherwise specified as inconsistent.(www.VBsemi.com)

Please note that some documents may still refer to Taiwan VBsemi RoHS Directive 2002/95 / EC. We confirm that all products identified as consistent with the Directive 2002/95 / EC European Directive 2011/65 /.

Taiwan VBsemi Electronics Co., Ltd. hereby certify that all of its products comply identified as halogen-free halogen-free standards required by the JEDEC JS709A. Please note that some Taiwanese VBsemi documents still refer to the definition of IEC 61249-2-21, and we are sure that all products conform to confirm compliance with IEC 61249-2-21 standard level JS709A.