

SIGN	DATE	DESCRIPTION	APPROVER
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item ① Insulating body: Thermoplastic (UL94V-0)
- Item ② contact pin: Brass Tin plated.
- Item ③ Spring clamp : Stainless steel
- Item ④ Side Cover : Thermoplastic (UL94V-0)

Electrical:




- Voltage rating: 300V
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 16-20
- Stranded wire(AWG): 16-20
- Wire strip length: 9-10mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C ±10°C/5 Sec

cULus

HB xx 41 x 1 xxxx G

No. OF POLES ————
02: 2 POLES
:
24: 24 POLES
COLOR ————
0: Black
2: RED
3: ORANGE
5: GREEN(RAL6018/T)
8: GREY

————— G: Pb<40000ppm
0000 Standard @ Logo
000A Standard ANY Logo
Any special item by
customer request,
please contact sales
department.



P.C.B Layout

POLE		2	3	4	5	6	7	8	9	10	11	12
A		7.92	11.88	15.84	19.80	23.76	27.72	31.68	35.64	39.60	43.56	47.52
B		3.96	7.92	11.88	15.84	19.80	23.76	27.72	31.68	35.64	39.60	43.56
Tol.	±0.15						±0.25					
POLE	13	14	15	16	17	18	19	20	21	22	23	24
A	51.48	55.44	59.40	63.36	67.32	71.28	75.24	79.20	83.16	87.12	91.08	95.04
B	47.52	51.48	55.44	59.40	63.36	67.32	71.28	75.24	79.20	83.16	87.12	91.08
Tol.	±0.30						±0.40					

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		HB 3.96 mm Without lever Series							
PART NO.		HBxx41x1xxxxG			DWG NO.		8HB0602		
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance		
			Kind 2009.11.03	Tony 2008.12.16			UNIT: mm		X. ±0.50
							SCALE: NONE		X.X ±0.30
					SHEET: 01/01		REV: B		X.XX ±0.10
									X° ±1°