




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REL PER ECO-18-014654	06SEP2018	JM	RB
	A1	REV PER ECO-18-016694	18OCT2018	JM	RB



2320915-2
SCALE 2:1
KEY B




2320915-3
SCALE 2:1
KEY C





2320915-4
SCALE 2:1
KEY D


COMPANY LOGO



SCALE 2:1



2320915-1 SHOWN
KEY A



SECTION A-A
WITH TPA IN CLOSED POSITION

1 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: GRAY

2 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: (SEE TABLE)

3 MATERIAL: SILICONE
COLOR: GREEN

4. RECOMMENDED WIRE DIAMETER RANGE IS 2.18 TO 3.67mm.

5. RECOMMENDED BACKSHELLS:

STRAIGHT EXIT

A. 2292862-1 SMOOTH WIRE EXIT
B. 2292862-2 NC16/NW13 CONDUIT WIRE EXIT
C. 2292862-3 NC12/NW10 CONDUIT WIRE EXIT

90° EXIT

D. 2302483-1 SMOOTH WIRE EXIT
E. 2302483-2 NC16/NW13 CONDUIT WIRE EXIT
F. 2302483-3 NC12/NW10 CONDUIT WIRE EXIT

6. RECOMMENDED SEAL PLUG: 776363-1

7. MATING CONNECTOR: 2320922-X.

D	ORANGE	2320915-4
C	PURPLE	2320915-3
B	BLUE	2320915-2
A	TAN	2320915-1
KEY	TPA COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. MCNEAL 09FEB2018	TE Connectivity		
DIMENSIONS: mm		CHK R. BALTER 09FEB2018			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R. BALTER 09FEB2018	NAME		
0 PLC ±		PRODUCT SPEC	CAP ASSEMBLY, 4 POSITION, STD DIA SEAL, HIGH TEMP, AMPSEAL 16		
1 PLC ±		108-2184			
2 PLC ±0.30		APPLICATION SPEC			
3 PLC ±		114-13065			
4 PLC ±		WEIGHT 14g			
ANGLES ±		CUSTOMER DRAWING			
FINISH -		SCALE 3:1			
		SHEET 1 OF 1			
		REV A1			