

1		2		3		4		5		6		7																																																																																																																																																																																																														
SIGN		DATE		DESCRIPTION						APPROVER																																																																																																																																																																																																																
△																																																																																																																																																																																																																										
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!																																																																																																																																																																																																																										
Material: - Terminal body (metal housing): Brass(CuZn) - Terminal screw: Steel Plated Zinc "- " slot type. - Wire guard: Stainless steel - Surface of solder tail: Tin plated - Insulator(housing): Thermoplastic (UL94V-0) Electrical: <table><tr><td>UL</td></tr><tr><td>Voltage rating: 125V</td></tr><tr><td>Current rating: 10A</td></tr><tr><td>Wire range:</td></tr><tr><td>Solid wire(AWG): 16-26</td></tr><tr><td>Stranded wire(AWG): 16-26</td></tr><tr><td>Torque: 1.7Lb-In</td></tr><tr><td>Screw: M2</td></tr><tr><td>Wire strip length: 5-6mm</td></tr><tr><td>Withstanding Voltage: 1.25 KV</td></tr><tr><td>Operating temperature: -40°C to +115°C</td></tr><tr><td>Soldering temperature: 250°C±10°C/5 Sec</td></tr><tr><td>Safety Approval:</td></tr></table> TE xx 0 1 x x xxxx G No. OF POLES 04: 4 POLES : 24: 24POLES Color 0 Black (RAL9005) 2 Red (RAL3001/D) 3 Orange(RAL2011/P) 4 Yellow(RAL1018/A) 5 Green(RAL6018/T) 6 Blue (RAL5015/A) 8 Grey(RAL7035/D) DIM A 3: 4.4mm 4: 3.8mm 5: 3.5mm G: Pb<40000ppm 0000: "@ " Logo (Standard) 000A: "ANYTEK" Mark Any special item by customer request. please contact sales department. <table><tr><td>POLE</td><td></td><td></td><td>4</td><td>5</td><td>6</td><td>7</td><td>8</td><td>9</td><td>10</td><td>11</td><td>12</td></tr><tr><td>A</td><td></td><td></td><td>14.00</td><td>17.50</td><td>21.00</td><td>24.50</td><td>28.00</td><td>31.50</td><td>35.00</td><td>38.50</td><td>42.00</td></tr><tr><td>B</td><td></td><td></td><td>10.50</td><td>14.00</td><td>17.50</td><td>21.00</td><td>24.50</td><td>28.00</td><td>31.50</td><td>35.00</td><td>38.50</td></tr><tr><td>Tol.</td><td colspan="5">±0.10</td><td colspan="6">±0.15</td></tr><tr><td>POLE</td><td>13</td><td>14</td><td>15</td><td>16</td><td>17</td><td>18</td><td>19</td><td>20</td><td>21</td><td>22</td><td>23</td><td>24</td></tr><tr><td>A</td><td>45.50</td><td>49.00</td><td>52.50</td><td>56.00</td><td>59.50</td><td>63.00</td><td>66.50</td><td>70.00</td><td>73.50</td><td>77.00</td><td>80.50</td><td>84.00</td></tr><tr><td>B</td><td>42.00</td><td>45.50</td><td>49.00</td><td>52.50</td><td>56.00</td><td>59.50</td><td>63.00</td><td>66.50</td><td>70.00</td><td>73.50</td><td>77.00</td><td>80.50</td></tr><tr><td>Tol.</td><td colspan="5">±0.20</td><td colspan="7">±0.30</td></tr></table> ANYTEK CUSTOMER COPY ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD <table><tr><td>TITLE</td><td colspan="12">TE 3.5mm Solid block series "- " Screw</td></tr><tr><td>PART NO.</td><td colspan="6">TExx01xxxxxxG</td><td>DWG NO.</td><td colspan="6">8TE0103</td></tr><tr><td>APPROVED</td><td>CHECKED</td><td>DESIGNED</td><td colspan="2">DRAWN</td><td colspan="2">CUST NO.</td><td colspan="3"></td><td colspan="3">Tolerance</td></tr><tr><td></td><td></td><td>Runner</td><td colspan="2">Runner</td><td colspan="2"></td><td colspan="2"></td><td colspan="2">UNIT: mm</td><td colspan="2">X. ±0.50</td></tr><tr><td></td><td></td><td>2010.03.26</td><td colspan="2">2010.03.26</td><td colspan="2"></td><td colspan="2"></td><td colspan="2">SCALE: NONE</td><td colspan="2">X.X ±0.30</td></tr><tr><td></td><td></td><td></td><td colspan="2"></td><td colspan="2"></td><td colspan="2">SHEET: 01/01</td><td colspan="2">REV.: C</td><td colspan="2">X.XX ±0.10</td></tr><tr><td></td><td></td><td></td><td colspan="2"></td><td colspan="2"></td><td colspan="2"></td><td colspan="2"></td><td colspan="2">X° ±1°</td></tr></table>														UL	Voltage rating: 125V	Current rating: 10A	Wire range:	Solid wire(AWG): 16-26	Stranded wire(AWG): 16-26	Torque: 1.7Lb-In	Screw: M2	Wire strip length: 5-6mm	Withstanding Voltage: 1.25 KV	Operating temperature: -40°C to +115°C	Soldering temperature: 250°C±10°C/5 Sec	Safety Approval:	POLE			4	5	6	7	8	9	10	11	12	A			14.00	17.50	21.00	24.50	28.00	31.50	35.00	38.50	42.00	B			10.50	14.00	17.50	21.00	24.50	28.00	31.50	35.00	38.50	Tol.	±0.10					±0.15						POLE	13	14	15	16	17	18	19	20	21	22	23	24	A	45.50	49.00	52.50	56.00	59.50	63.00	66.50	70.00	73.50	77.00	80.50	84.00	B	42.00	45.50	49.00	52.50	56.00	59.50	63.00	66.50	70.00	73.50	77.00	80.50	Tol.	±0.20					±0.30							TITLE	TE 3.5mm Solid block series "- " Screw												PART NO.	TExx01xxxxxxG						DWG NO.	8TE0103						APPROVED	CHECKED	DESIGNED	DRAWN		CUST NO.					Tolerance					Runner	Runner						UNIT: mm		X. ±0.50				2010.03.26	2010.03.26						SCALE: NONE		X.X ±0.30									SHEET: 01/01		REV.: C		X.XX ±0.10													X° ±1°	
UL																																																																																																																																																																																																																										
Voltage rating: 125V																																																																																																																																																																																																																										
Current rating: 10A																																																																																																																																																																																																																										
Wire range:																																																																																																																																																																																																																										
Solid wire(AWG): 16-26																																																																																																																																																																																																																										
Stranded wire(AWG): 16-26																																																																																																																																																																																																																										
Torque: 1.7Lb-In																																																																																																																																																																																																																										
Screw: M2																																																																																																																																																																																																																										
Wire strip length: 5-6mm																																																																																																																																																																																																																										
Withstanding Voltage: 1.25 KV																																																																																																																																																																																																																										
Operating temperature: -40°C to +115°C																																																																																																																																																																																																																										
Soldering temperature: 250°C±10°C/5 Sec																																																																																																																																																																																																																										
Safety Approval:																																																																																																																																																																																																																										
POLE			4	5	6	7	8	9	10	11	12																																																																																																																																																																																																															
A			14.00	17.50	21.00	24.50	28.00	31.50	35.00	38.50	42.00																																																																																																																																																																																																															
B			10.50	14.00	17.50	21.00	24.50	28.00	31.50	35.00	38.50																																																																																																																																																																																																															
Tol.	±0.10					±0.15																																																																																																																																																																																																																				
POLE	13	14	15	16	17	18	19	20	21	22	23	24																																																																																																																																																																																																														
A	45.50	49.00	52.50	56.00	59.50	63.00	66.50	70.00	73.50	77.00	80.50	84.00																																																																																																																																																																																																														
B	42.00	45.50	49.00	52.50	56.00	59.50	63.00	66.50	70.00	73.50	77.00	80.50																																																																																																																																																																																																														
Tol.	±0.20					±0.30																																																																																																																																																																																																																				
TITLE	TE 3.5mm Solid block series "- " Screw																																																																																																																																																																																																																									
PART NO.	TExx01xxxxxxG						DWG NO.	8TE0103																																																																																																																																																																																																																		
APPROVED	CHECKED	DESIGNED	DRAWN		CUST NO.					Tolerance																																																																																																																																																																																																																
		Runner	Runner						UNIT: mm		X. ±0.50																																																																																																																																																																																																															
		2010.03.26	2010.03.26						SCALE: NONE		X.X ±0.30																																																																																																																																																																																																															
							SHEET: 01/01		REV.: C		X.XX ±0.10																																																																																																																																																																																																															
											X° ±1°																																																																																																																																																																																																															