







N=Number of contacts
Dimension A&B

DIM A	N×10+3.5
DIM B	(N-1)×10

Poles	Tol.	Dim A&B
4p		±0.20
5-10p		±0.30
11-24p		±0.40
25-30p		±0.50

SIGN	DATE	DESCRIPTION	APPROVER
△	2/07'06	Wire range is changed from 22-14 AWG to 22-12 AWG	Tony
△	2/07'06	Part No. is changed	Tony
△	3/13'06	Dimension is changed from 5.7 to 3.9	Tony
△	2006.08.3	Screw torque value is changed from 10.4Lb-in to 12Lb-in	梁仁松
△	2006.08.3	Approval is changed	梁仁松
△	06 /05'07	Material is changed	Lucy
△	3/30'09	Structure changed	JODY
△	3/30'09	Temperature changed from -40~105℃ to -40~115℃	JODY
△	11/13'12	Change the screw plating specification	Jacky
△	11/13'12	Change the dimensional tolerance	Jacky
△	11/13'12	Add the dimensional label	Jacky
△	08/25'14	The dimensional tolerance is changed from 17.4±0.30 to 17.4 ^{+0.80} _{-0.30}	Airy min

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

MATERIALS ELECTRICAL
RATED VOLTAGE & CURRENT: 300 V, 20 A
WITHSTAND VOLTAGE: AC 2000 V/Min
INSULATION RESISTANCE: 1000 MΩ OR MORE AT DC 500 V
OPERATING TEMPERATURE RANG: △ -40 °C ~ +115 °C
△ SCREW TORQUE VALUE: 12Lb-In.
△ WIRE RANGE: 22 - 12 AWG
△ 1) MOLDED PARTS: THERMOPLASTIC, UL 94 V-0 BLACK
2) TERMINAL: BRASS, 0.8t, Tin PLATED
△ 3) TERMINAL SCREWS: STEEL, M3.5
4) COVER MATERIAL: PC

△ APPROVAL: 
△ PART NO:

Critical dimension:

YK 601 xx 2 x x 00G

NO. OF POLES

04: 4 POLES
05: 5 POLES
06: 6 POLES

30: 30 POLES

G:RoHS compliant(lead<4%)
in copper alloy

MARK

0: "@" MARK

1: "ANY" MARK

TERMINAL & SCREW PLATED

0: TERMINAL & SCREW: G/F

△ 1: TERMINAL: G/F, SCREW: Zinc


2: TERMINAL: Sn, SCREW: G/F

△ 3: TERMINAL: Sn, SCREW: Zinc

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		YK-601 Without Flange&With Cover Series(4-30P)					
PART NO.	YK601xx2xx00G			DWG NO.	8YK0001-601		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Airy min 2014.08.25	Airy min 2014.08.25		UNIT: mm	X.	±0.50
					SCALE: NONE	X.X	±0.30
						X.XX	±0.10
				SHEET: 01/01	REV.: H	X°	±1°