


$\Delta$   
 N = Number of poles  
 Dim A =  $N \times 8.25 + 2.0$   
 Dim B =  $(N - 1) \times 8.25$

| Poles  | Tol. | Dim A&B    |
|--------|------|------------|
| 2-5p   |      | $\pm 0.20$ |
| 6-10p  |      | $\pm 0.25$ |
| 11-16p |      | $\pm 0.35$ |
| 17-24p |      | $\pm 0.40$ |
| 25-30p |      | $\pm 0.50$ |

| SIGN     | DATE      | DESCRIPTION                                         | APPROVER |
|----------|-----------|-----------------------------------------------------|----------|
| $\Delta$ | 03/11/09  | Change the plating specification                    | Jason    |
| $\Delta$ | 06/04 '11 | Critical dimension is changed.                      | Tason    |
| $\Delta$ | 06/04 '11 | The Wire Range is changed from 20-12AWG to 22-12AWG | Tason    |
| $\Delta$ | 06/04 '11 | The tolerance table is changed.                     | Tason    |
| $\Delta$ | 11/27 '12 | Change the screw plating specification              | Jacky    |
| $\Delta$ | 12/07 '13 | Change the withstand voltage and current            | Jacky    |

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

MATERIALS ELECTRICAL: cULus / CQC  $\Delta$   
 RATED VOLTAGE & CURRENT: 300 V, 20 A/300 V, 32 A  $\Delta$   
 WITHSTAND VOLTAGE: AC 2500 V/Min  $\Delta$   
 INSULATION RESISTANCE: 1000 M $\Omega$  OR MORE AT DC 500 V  
 OPERATING TEMPERATURE RANG: -40 °C ~ +115 °C  
 SCREW TORQUE VALUE: 8.8 Lb-In  
 WIRE RANGE: 22 - 12 AWG  $\Delta$   
 1) MOLDED PARTS: POLYIMIDE 66, UL 94 V-0 BLACK  
 2) TERMINAL: BRASS, 0.8t, Tin PLATED  
 3) TERMINAL SCREWS: STEEL, M3

$\Delta$  Critical dimension:  
 APPROVAL:  $\Delta$

YK 333 xx 0 x x 00G

NO. OF POLES  
 02: 2 POLES  
 03: 3 POLES  
 04: 4 POLES  
 :  
 30: 30 POLES

TERMINAL & SCREW PLATED  
 0: TERMINAL & SCREW: G/F  
 1: TERMINAL: G/F, SCREW: Zinc  
 2: TERMINAL: Sn, SCREW: G/F  
 3: TERMINAL: Sn, SCREW: Zinc

G:RoHS compliant  
 (lead<4%)  
 in copper alloy  
 MARK  
 0: "@ " MARK  
 1: "ANY " MARK

**ANYTEK**

**CUSTOMER COPY**

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

|          |  |               |                     |                     |                                                                                       |                        |             |  |           |                     |  |
|----------|--|---------------|---------------------|---------------------|---------------------------------------------------------------------------------------|------------------------|-------------|--|-----------|---------------------|--|
| TITLE    |  | YK-333 Series |                     |                     |                                                                                       | PART NO. YK333xx0xx00G |             |  |           | DWG NO. 8YK0001-333 |  |
| APPROVED |  | CHECKED       | DESIGNED            | DRAWN               | CUST NO.                                                                              |                        |             |  | Tolerance |                     |  |
|          |  |               | Jacky<br>2013.12.07 | Jacky<br>2013.12.07 |  |                        | UNIT: mm    |  | X.        | ±0.50               |  |
|          |  |               |                     |                     |                                                                                       |                        | SCALE: NONE |  | X.X       | ±0.30               |  |
|          |  |               |                     |                     | SHEET: 01/01                                                                          |                        | REV.: F     |  | X.XX      | ±0.10               |  |
|          |  |               |                     |                     |                                                                                       |                        |             |  | X°        | ±1°                 |  |