






Material

- Item ① Insulator body: Thermoplastic (UL94V-0)
- Item ② Insulating cover :Thermoplastic (UL94V-0)
- Item ③ Contact pin : Brass.Tin plated
- Item ④ Wire guard: Stainless steel
- Item ⑤ Pad board: Thermoplastic (UL94V-0)

Electrical:

- Voltage rating: 300V
- Current rating: 8A
- Wire range:
- Solid wire(AWG): 12-28
- Stranded wire(AWG): 12-28
- Wire strip length: 8-9mm
- Withstanding Voltage: 16KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Critical dimension: ∇

HM XX 40 x 0 XXXX G

No. OF POLES

- 01: 1 POLES
- 02: 2 POLES

16: 16 POLES

- COLOR
- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- 3 Orange(RAL2011/P)
- 4 Yellow(RAL1018/A)
- 5 Green(RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey(RAL7004/P)
- 9 White(RAL1102)
- C Multiple colors

- 0000 Standard @ Logo
- 000A Standard ANY Logo
- Any special item by customer request, please contact sales department.

RoHS compliant (lead<4%)
In copper Alloy

N=NUMBER OF POLES

Dim L	(N-1)*7.62+6.58
Dim B	(N-1)*7.62

POLES	Dim L	Dim B
1p	±0.15	±0.15
2p-4p	±0.2	±0.15
5p-8p	±0.3	±0.25
9p-12p	±0.4	±0.35
13p-16p	±0.45	±0.4

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO.,LTD

TITLE		DWG NO.		Tolerance	
HM 7.62 mm Series Dip solder		8HM0103		±0.50	
PART NO.	HMxx40xxxxxG	CUST NO.		UNIT: mm	XX ±0.30
APPROVED	CHECKED	DESIGNED	DRAWN	SCALE: NONE	XX ±0.10
	Da cheng 2013.05.28	Da cheng 2013.05.28		SHEET: 01/01	REV: D