

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

FEB ,2005.

© COPYRIGHT 2005 By --

ALL RIGHTS RESERVED.

LOC
ES

DIST





REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	G2	REVISED PER ECO-11-005033	29MAR11	RK	HMR

HOW TO MATE AND UNMATE




MATE: ① → ④
UNMATE: ⑤ → ⑦

MODULE HEIGHT



(APPLIED TO SHEET 1-2)

- MATERIAL ; HOUSING:HIGH TEMPERATURE THERMO PLASTIC
UL94V-0, COLOR : BLACK
CONTACT : COPPER ALLOY
LOCK LEVER : STAINLESS STEEL
- FINISH ; CONTACT : Au PL. IN CONTACT AREA AND SOLDERING
AREA ON NICKEL UNDER PL.
SOLDERING AREA(LOCK LEVER) : TIN PL.
- MECHANICAL KEY POSITION OF CONNECTOR SEE TABLE.
- TOLERANCES NON-CUMMURATIVE.
- COPLANARITY: 0.1MAX
- THE FLOATING VALUE BY SOLDERING IS NOT INCLUDED.
- NOT MATING CONDITION.
- IF THE MODULE DOESN'T INSERT AND LOCK IN THE LATCH SMOOTHLY,
OPEN WIDE BOTH LATCHES BY MANUAL. AND THE MODULE MUST BE
INSERTED AND LOCKED IN THE LATCH.
- VACUUM AREA MUST BE FLAT AND NO HOT MARK.

DETAIL J
(SCALE 5:1)DETAIL H
(SCALE 5:1)

GENERAL TOLERANCE
10 ≥ : ±0.2
30 ≥ > 10: ±0.25
100 ≥ > 30: ±0.3
ANGLES: ±3°

AVAILABLE	1.8V (DDR2)	17.55	2.4	2.7	200	1827341-4
NOT AVAILABLE	2.5V (DDR1)	18.45	1.5	1.8	200	-
TOOLING STATUS	POWER SUPPLY (TYPE)	D5	D4	D3	POS	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: MM	TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±	1 PLC ±
2 PLC ±	3 PLC ±
4 PLC ±	ANGLES ±
MATERIAL	FINISH

DWN T.FUMIKURA CHK	04FEB05
APVD	
PRODUCT SPEC 108-5701	
APPLICATION SPEC	
WEIGHT	
CUSTOMER DRAWING	

TE Connectivity

NAME DDR1 & DDR2 SODIMM SOCKET 0.6mm PITCH 200POS 8mm HEIGHT STANDARD TYPE (LATCH DIRECT SOLDERING TYPE)			
SIZE A3	CAGE CODE 00779	DRAWING NO C-1827341	RESTRICTED TO
SCALE 2:1		SHEET 1 OF 4	REV G2

1470-19 (3/11)